

# WAGO Multi Marking System WMB Horizontal Marking

	<b>Horizontal marking</b> <b>Consecutive numbers each strip</b>  <b>10 strips with 10 markers per card</b> <b>for terminal block widths</b> <b>4 – 4.2 mm und 5 – 12 mm</b>	
--	--	--



Marking per card	Item No.	Item No.	Pack. unit pcs
	<b>Marker width</b>		
	<b>4 – 4.2 mm</b>	<b>5 – 5.2 mm</b>	
1 ... 10 (10x)	793-4502	793-5502	5 cards
11 ... 20 (10x)	793-4503	793-5503	5 cards
21 ... 30 (10x)	793-4504	793-5504	5 cards
31 ... 40 (10x)	793-4505	793-5505	5 cards
41 ... 50 (10x)	793-4506	793-5506	5 cards
51 ... 60 (10x)	793-4569	793-5569	5 cards
61 ... 70 (10x)	793-4570	793-5570	5 cards
71 ... 80 (10x)	793-4571	793-5571	5 cards
81 ... 90 (10x)	793-4572	793-5572	5 cards
91 ... 100 (10x)	793-4573	793-5573	5 cards
<b>1 ... 50 (2x)</b>	<b>793-4566</b>	<b>793-5566</b>	5 cards
51 ... 100 (2x)	793-4507	793-5507	5 cards
101 ... 150 (2x)	793-4508	793-5508	5 cards
151 ... 200 (2x)	793-4509	793-5509	5 cards
201 ... 300 (1x)	793-4510	793-5510	5 cards
301 ... 400 (1x)	793-4511	793-5511	5 cards
401 ... 500 (1x)	793-4512	793-5512	5 cards
501 ... 600 (1x)	793-4513	793-5513	5 cards
601 ... 700 (1x)	793-4514	793-5514	5 cards
701 ... 800 (1x)	793-4515	793-5515	5 cards
801 ... 900 (1x)	793-4516	793-5516	5 cards
901 ... 1000 (1x)	793-4517	793-5517	5 cards
1 ... 9, ; (10x)	793-4565	793-5565	5 cards
<b>L1, L2, L3, N, PE, L1, L2, L3, N, PE (10x)</b>	<b>793-4472</b>	<b>793-5472</b>	5 cards
R, S, T, U, V, W, X, Y, Z, Mp (10x)	793-4544	793-5544	5 cards
A, B, P, N, PE, PEN, L1, L2, L3, ⊕ (10x)	793-4545	793-5545	5 cards
<b>for double deck terminal blocks</b>	<b>for double deck terminal blocks</b>		
1, 3, 5, 7, 9, 11, ... 99 und 2, 4, 6, 8, 10, 12, ... 100 (1x)	–	793-5599	5 cards
<b>for triple deck terminal blocks</b>	<b>for triple deck terminal blocks</b>		
1, 4, 7, ... 99 (1x)	–	794-5557	5 cards
100, 103, 106, ... 198 (1x)	–	794-5558	5 cards
	<b>WMB Inline</b>	<b>2009-115</b>	
	(see page 40)		



Stretching of a strip, stretchable from 4 mm up to 4.2 mm for series 2001 stretchable from 5 mm up to 5.2 mm for series 2002



Separation of an individual marker from the strip, for series > 2002