

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.



LOC  
J

DIST

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-10-010439	10JUN2010	HMR	T.M



AS SHOWN: 1903112-2

△ COPPER ALLOY: FINISH; CONTACT AREA Au 0.38μmMIN, OVER Ni 1.27μmMIN △ 銅合金: 下地; 全面ニッケルめっき1.27μm以上, 接点部; 金めっき0.38μm以上	1903112-2
MATERIAL (材料)	PART NO (型番)

1. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

1. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: ㎜ mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±3° 0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ±	DWN M. MAEBASHI 11APR2006 CHK T. KUDO 11APR2006 APVD D. MITSUGI 11APR2006	WIRE RANGE 包合電線断面積 mm <sup>2</sup> 0.08~0.38	INSULATION DIA 被覆外径 φ1.08~φ1.6
MATERIAL 材料	FINISH 仕上	PRODUCT SPEC 製品規格 108-78268 APPLICATION SPEC 取付適用規格 108-78268	Tyco Electronics Corporation Kawasaki, Japan	
		WEIGHT 0.126 g	NAME 名称 DYNAMIC D1000 SERIES TAB CONTACT Au M-TYPE REEL	RESTRICTED TO
		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779
			DRAWING NO 番号 C=1903112	SCALE 尺度 10:1
			SHEET 1	OF 1
			REV B	