

# Specifications for TLS 2200/TLS PC Link DuraSleeve Wire Marking Inserts

|                                      |   |
|--------------------------------------|---|
| <b>Application</b>                   | Wire & Cable Marking  |
| <b>Article No.</b>                   | 217026  |
| <b>Brady Material No.</b>            | <a href="#">B-7596</a>  |
| <b>Material Type</b>                 | Vinyl Tag   |
| <b>Colour</b>                        | White   |
| <b>Finish</b>                        | Matt  |
| <b>Description</b>                   | DuraSleeve® markers for the TLS 2200® & TLSPC LINK™ printers. Brady DuraSleeve® markers create a durable legend. The DuraSleeve wire marking system provides printable inserts that can easily be inserted into a clean carrier. The legend can be changed before or after termination. |
| <b>Max. Service Temp. °C</b>         | 100   |
| <b>Max. Wire/Cable Diameter (mm)</b> | 10.00   |
| <b>Order Reference</b>               | PTDSU-15-7596   |
| <b>Printer Compatibility</b>         | BMP71; TLS2200; TLSPC Link  |
| <b>Ribbon Series</b>                 | R4310   |
| <b>Shape</b>                         | Rectangle   |
| <b>Size - Height (mm)</b>            | 4.20  |
| <b>Size - Width (mm)</b>             | 15.00   |
| <b>Total Qty per Pack</b>            | 2500 Insert(s) / Box  |
| <b>Industry</b>                      | Data & Telecommunications;Electrical  |
| <b>Min. Service Temp. °C</b>         | -40   |
| <b>QTY. per Row</b>                  | 1   |
| <b>Thickness (mm)</b>                | 0.2   |