

Vigi iC60 - earth leakage add-on block - 2P - 25A - 10mA - AC type

Local distributor code:

402643434 A9V10225

EAN Code: 3606480087462

Main

Range	Acti9	
Product name	Acti9 Vigi iC60	
Product or component type	Add-on residual current device	
Device short name	Vigi iC60	
Poles description	2P	
[In] rated current	25 A	
Earth-leakage sensitivity	10 mA	
Earth-leakage protection time delay	Instantaneous	
Earth leakage protection type	Type AC	
Network type	AC	
Network frequency	50/60 Hz	
[Ue] rated operational voltage	230240 V AC 50/60 Hz conforming to EN/IEC 61009-1 230240 V AC 50/60 Hz conforming to IEC/EN 61009-2-1	
Standards	EN 61009-1 IEC 61009-1	
9 mm pitches	3	

Complementary

Device location in system	Outgoer	
Residual current tripping technology	Voltage independent	
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2	
Range compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 Reflex iC60	
Product compatibility	Single terminal	
Local signalling	Trip indicator	
Mounting mode	Clip-on	
Mounting support	DIN rail	
Electrical connection to mcb	By screws	
Comb busbar and distribution block compatibility	Bottom: YES	
Height	91 mm	
Width	63 mm	

Depth	73.5 mm	
Net weight	0.165 kg	
Connections - terminals	Tunnel type terminal downside for 1 cable(s) 125 mm² rigid without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible with cable end	
Wire stripping length	14 mm for bottom connection	
Tightening torque	2 N.m bottom	

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529	
Pollution degree	3 conforming to IEC 60947-2	
Electromagnetic compatibility	8/20 μs impulse withstand, 250 A conforming to IEC 61009-1	
Ambient air temperature for operation	-560 °C	
Ambient air temperature for storage	-4085 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.8 cm
Package 1 Length	11.5 cm
Package 1 Weight	153.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.599 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	6
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	42d9fa7e-1604-4ebd-8742-78b281843dbb
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins