

## Features

- UL approved Nylon 66
- UL94V-2 flame rated
- Low Smoke, Halogen Free
- Max operating temperature 85°C

## RS PRO Cable Ties

RS Stock No.: 0834130



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Designed for demanding cable management tasks, this cable tie offers exceptional strength and reliability. Made from fire-resistant Nylon 66 (UL-approved) with a flame-rating of 94V-2, it's built to deliver robust performance even in harsh environments. Whether in construction, telecom, data centres, or high-power installations, this cable tie helps keep things neat, safe, and resilient.

## General Specifications

|                               |                                                        |
|-------------------------------|--------------------------------------------------------|
| Series                        | Nylon Cable Ties                                       |
| Type                          | Non-Releasable                                         |
| Colour                        | Black                                                  |
| Material                      | Nylon 66                                               |
| Finish                        | Smooth                                                 |
| Application                   | Designed for quick installation and bundling of cables |
| Resistant To                  | Not specified                                          |
| UV Resistant                  | No                                                     |
| Minimum Operating Temperature | Not specified                                          |
| Maximum Operating Temperature | 85°C                                                   |
| Fire Behaviour                | Self-Extinguishing                                     |
| Quantity                      | 100                                                    |

## Mechanical Specifications

|                  |       |
|------------------|-------|
| Length           | 550mm |
| Width            | 8.0mm |
| Tensile Strength | 222N  |

## Approvals

|              |      |
|--------------|------|
| Declarations | RoHS |
|--------------|------|

|               |    |
|---------------|----|
| Standards Met | UL |
|---------------|----|

