



Brand of NTN corporation

Technical data

USPP204

Bearing units




Sheet metal housing, radial insert ball bearing with socket set screws, single lip seal

KIT CONTENT

US204G2, PP204

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	31,7 mm
A1 - Housing top width	21,6 mm
B - Width of Inner Ring	25 mm
d - Shaft diameter	20 mm
H - Distance mounting base to centerline spheric. seating diam.	25,4 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

H1 - Housing foot height	2,4 mm
H2 - Housing height	49,9 mm
J - Mounting holes distance	76 mm
L - Housing length	98,4 mm
N - Mounting hole dimension	9 mm
S - Distance front side/bearing centre	7 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	12800000 mN
C0 - Static load rating	6650000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	0,22 kg
Recommended tightening torque for set screw	5.5 N-m

