



Hand protection

VENICUTD00

LONG-LASTING CUT WORK

Uncoated level D cut-resistant glove, combining comfort and flexibility, ideal for food industry.



Specific benefits



Durability

- Tested before and after washing: performance unchanged



Easy to use

- Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use



Hygiene

- Washable glove, so it can be reused
- Reduces perspiration thanks to its excellent breathability



Performance

- Lightweight for optimal dexterity



Compatibility

- Compatible with food

Applications

- Public works
- Manufacturing/Transformation
- Maintenance
- Automotive
- Mining
- Temporary work

Certifications and norms



EN 388
4 X 4 3 D



Protects against risks



Cutting



Wearing



Hand protection

VENICUTD00

LONG-LASTING CUT WORK

Uncoated level D cut-resistant glove, combining comfort and flexibility, ideal for food industry.

Standards - Details



EN388:2016+A1:2018

4 [0-4] ABRASION RESISTANCE
X [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
3 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted uncoated glove
Mechanical glove kind	Knitted
Gauge	15
Benefits element	Reach, Washable, Vendor pack
Color	Blue-White
Size	6, 7, 8, 9, 10, 11
Type of packaging	in individual bags

Product care

- Flat drying



Safety gloves

VENICUTD00

LONG-LASTING CUT WORK

Uncoated level D cut-resistant glove, combining comfort and flexibility, ideal for food industry.

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VECUTD00BL06	Blue-White	06	VENICUTD00	3295249296780	13295249296787	60	12	3.8 kg	31.0 cm	51.2 cm	14.8 cm
VECUTD00BL07	Blue-White	07	VENICUTD00	3295249296797	13295249296794	60	12	3.8 kg	30.8 cm	51.0 cm	14.8 cm
VECUTD00BL08	Blue-White	08	VENICUTD00	3295249296803	13295249296800	60	12	4.2 kg	31.0 cm	51.2 cm	14.6 cm
VECUTD00BL09	Blue-White	09	VENICUTD00	3295249296810	13295249296817	60	12	4.5 kg	34.2 cm	53.0 cm	16.4 cm
VECUTD00BL10	Blue-White	10	VENICUTD00	3295249296827	13295249296824	60	12	4.9 kg	34.2 cm	53.2 cm	16.4 cm
VECUTD00BL11	Blue-White	11	VENICUTD00	3295249296834	13295249296831	60	12	5.1 kg	34.0 cm	53.0 cm	16.8 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height