



Cut



Medium Duty

Resilient, cut-resistant polyurethane gloves, with dirt masking for long-lasting wear

- **Heightened durability:** HyFlex® 11-751 PU-coated gloves offer exceptional durability, meeting ANSI/ISEA 105-2024 Abrasion Level 6 and EN Abrasion Level 4 measures
- **Advanced protection:** INTERCEPT™ Cut Resistance Technology yarn provides ANSI/ISEA 105-2024 CUT A4 and EN ISO C standards, enhancing safety and reducing workplace injuries
- **Considered aesthetics:** HyFlex® 11-751 industrial gloves have been designed with integrated dirt masking, for longer wear
- **Certified performance:** These safety gloves officially comply with Centexbel standards EN 420, for general requirements, and EN 388, for mechanical hazards
- **Guaranteed convenience:** For added practicality, HyFlex® 11-751 industrial working gloves are available in vend pack form, for easy access and re-application



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket

Applications

- General maintenance
- Hardware assembly
- Machining / Stamping / Cutting
- Raw material handling
- Seat and frame build
- Compatible with consumer and industrial touchscreens

Key Features

- **Durable PU coating:** Offers ANSI/ISEA 105-2024 ABRASION LEVEL 6 and EN ABRASION LEVEL 4 resistance
- **INTERCEPT™ Cut Resistance:** ANSI/ISEA 105-2024 CUT A4 and EN ISO C protection
- **Dirt masking:** Stains and marks hidden, ideal for messy applications

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4X43C



STANDARD
100

1408033
Centexbel

Technologies



INTERCEPT™
Cut Resistance Technology



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-751	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: HPPE, Fiber glass, Nylon, Spandex Cuff Style: Knitwrist	10	5, 6, 7, 8, 9, 10, 11	224-269mm, 8.81 - 10.59 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.