




Visual Signals **XENON** **BEACONS**

Industrial Xenon Beacons > X201SD-200S Series

Product overview

The X201SD/200S Series utilises a discharge capacitor and converter circuit to ignite xenon gas inside a tube, resulting in a brilliant flash of light. Xenon gas ignites virtually instantaneously so maximum brightness is obtained immediately. Xenons have an

added advantage of low current consumption combined with a reasonable life span. The X201SD/200S Series provides a 360-degree light output. The series are IP66 rated making them ideal for marine applications. The X201SD has double flash as standard. Xenon beacons are one of the most efficient, effective and brightest visual signals available.



FEATURES

- Continuously rated
- Suitable for surface mounting
- Ideal for areas of high vibration
- Very robust construction
- 360° visibility
- IP66

MATERIAL

UV Stable Polycarbonate Lens
Zinc Cast Metal Base

Code No:	Voltage:	Light Source:	Current:
X201SD-12	12-48v Dc ---	Xenon 11J	1.50 A •
X200S-240	240v Ac ~	Xenon 11J	0.05 A

• At 24v Dc ---



Kg 0.92

50/60 **Hz**

°C -35+66

IP 66

FPM 120DC
60AC

MARINE

APPROVAL AND
CONFORMITIES



ADD THE FOLLOWING LENS CODES TO
THE PRODUCT CODE WHEN ORDERING

01

02



INDUSTRIAL