
Features

- Grade 10 container hook for bottom lifting of containers
- Available in Left, Right and Straight versions
- Suitable for 20mm lifting chain
- 16t Working Load Limit
- Luminous red powder painted finish for easy identification

RS PRO Container Hook Range



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Container Hook Range

The RS PRO Container Hooks are a Grade 10 lifting chain component designed for bottom lifting of containers. It is an easy-to-use and cost-effective component for container lifting applications and is available in **Left**, **Right** and **Straight** versions to suit different lifting configurations.

The **Left and Right container hooks** are designed for use with a spreader beam and four inclined sling legs, using two left-hand and two right-hand hooks at **45° ±15°**. The **Straight container hook** is designed for use with a spreader frame and four vertical sling legs at **0° ±15°**.

These hooks are suitable for use with **20mm chain** and have a **Working Load Limit of 16t**. They are manufactured from high-strength **Grade 10 alloy steel** and finished in luminous red powder paint for durability and easy identification.
Each component is type tested and fatigue rated to **20,000 cycles at 1.5 times the WLL**, with full traceability through batch marking. It meets **EN 1677-1 +25% WLL** and **AS 3776**, with a safety factor of **4:1**.

The component may also be used with Grade 8 chain to **EN 818-2**, provided the complete lifting assembly is rated as Grade 8 in accordance with **EN 818-4**.

General Specifications

Product Type	Lifting Hooks
Sub Type	Container Hook
Material	Grade 10 Alloy steel
Working Load Limit	See details below
Weight	See details below
Standards/Approvals	EN1677

Stock No.	Product Name	Working Load Limit	Weight (kg)
904899	Container Lifting Hook	16t	4
904900	Container Lifting Hook	16t	4
904901	Container Lifting Hook	16t	4

Approvals

Declarations	REACH DoC and 2.2 Certificate
Standards Met	EN1677

Similar Prducts

Stock No.	Brand	Product Name	Product Type	Working Load Limit	Weight (kg)
904899	RS PRO	Lifting Hook	Container	16t	4
904900	RS PRO	Lifting Hook	Container	16t	4
904901	RS PRO	Lifting Hook	Container	16t	4
904897	RS PRO	Lifting Hook	Connecting Link	1.4t	0.08
Stock No.	**Brand**	**Product Name**	**Product Type**	**Working Load Limit**	**Weight (kg)**
904898	RS PRO	Lifting Hook	Connecting Link	2.5t	0.18
904888	RS PRO	Lifting Hook	Connecting Link	4t	0.34
904890	RS PRO	Lifting Hook	Connecting Link	6.7t	0.68
904891	RS PRO	Lifting Hook	Connecting Link	10t	1.22
904892	RS PRO	Lifting Hook	Connecting Link	16t	2.13
904893	RS PRO	Lifting Hook	Connecting Link	19t	3
904894	RS PRO	Lifting Hook	Connecting Link	26.5	5.22
904896	RS PRO	Lifting Hook	Connecting Link	40	9.55
904910	RS PRO	Lifting Hook	Self-Lock w/ Eye	1.4	0.5
904911	RS PRO	Lifting Hook	Self-Lock w/ Eye	2.5	0.9
904903	RS PRO	Lifting Hook	Self-Lock w/ Eye	4	1.5
904904	RS PRO	Lifting Hook	Self-Lock w/ Eye	6.7	2.7
904905	RS PRO	Lifting Hook	Self-Lock w/ Eye	10	5.7
904906	RS PRO	Lifting Hook	Self-Lock w/ Eye	16	7.9
904907	RS PRO	Lifting Hook	Self-Lock w/ Eye	19	11.2
904908	RS PRO	Lifting Hook	Self-Lock w/ Eye	26.5	20.5
904909	RS PRO	Lifting Hook	Self-Lock w/ Eye	40	40.4
904879	RS PRO	Lifting Hook	Sling Hook	1t	0.7
904880	RS PRO	Lifting Hook	Sling Hook	2t	1.3

904881	RS PRO	Lifting Hook	Sling Hook	3t	2.3
904882	RS PRO	Lifting Hook	Sling Hook	5t	4.6
904886	RS PRO	Lifting Hook	Sling Hook with Swivel	1.4	0.65
904887	RS PRO	Lifting Hook	Sling Hook with Swivel	2.5	0.95
Stock No.	**Brand**	**Product Name**	**Product Type**	**Working Load Limit**	**Weight (kg)**
904883	RS PRO	Lifting Hook	Sling Hook with Swivel	4	1.7
904884	RS PRO	Lifting Hook	Sling Hook with Swivel	6.7	3.1
904885	RS PRO	Lifting Hook	Sling Hook with Swivel	10	5.4
904877	RS PRO	Lifting Hook	Sling Hook with Eye	1.4t	0.27
904878	RS PRO	Lifting Hook	Sling Hook with Eye	2.5t	0.65
904912	RS PRO	Lifting Hook	Sling Hook with Eye	4t	1.22
904913	RS PRO	Lifting Hook	Sling Hook with Eye	6.7t	2.43
904871	RS PRO	Lifting Hook	Sling Hook with Eye	10t	3.81
904872	RS PRO	Lifting Hook	Sling Hook with Eye	16t	6.2
904874	RS PRO	Lifting Hook	Sling Hook with Eye	19t	11.5
904875	RS PRO	Lifting Hook	Sling Hook with Eye	26.5t	12.2
904876	RS PRO	Lifting Hook	Sling Hook with Eye	40t	17.5