





Datasheet

Foot switch, maintained action switch



RS Article No. 1253708

Specifications:

Operating Frequency: Insulation Resistance: Contact Resistance: Rated Current/Voltage: Dielectric Strength:

Service Life: Operating Temperature: Degree of Protection: Size (LXWXH): 60 ops/min >100MQ@500V DC <25mQ(initial) 20A:1-1/2HP 125VAC,2HP 250VAC 1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts Mechanically 1X10 6Electrically 5X105 - $30 \sim +80^{\circ}$ C (- $22 \sim 176^{\circ}$ F) IP20 142.50X89X54mm

Features:

- Robust Zinc metal die cast body
- UL/CSA/CE Certified
- SPDT TYPE
- Maintained type
- M20 Conduit type

