



# Datasheet

## USB A Power Adapter

### 5Vdc 5W Euro Plugtop

RS Stock No.: 8280213

ENGLISH



#### Features

- Universal AC Input
- Euro Plugtop
- Small & Compact Design
- USB A Output
- Over Voltage, Over Current & Over Temp. Protections
- ErP Level V
- RoHS Compliant
- MTBF >50,000 hours

RS Stock Number	Manufacturers P/N	Output Voltage	Output Current (Min)	Output Current (Max)	Power (Watts)	Line Regulation	Voltage Tolerance	Ripple & Noise (mV- p-p)
8280213	T5225ST	+/- 5Vdc	0A	1A	5W	+/-1%	+/-5%	100mV

#### Input

- Rated Input 100-240Vac
- Rated Input Frequency 50-60Hz
- Input Current 300mA
- Inrush Current 75A at 240Vac
- Efficiency >60%
- Euro Plugtop

#### Output

- USB Output

#### Environmental

- Operating Temperature -20°C to 45°C
- Storage Temperature -10°C to 75°C
- Operating Humidity 20% to 80%
- Storage Humidity 20% to 80%

#### Casing

- Dimensions 56.8mm x 39mm x 26mm
- Weight 82g (approx.)

