



**2 YEARS**  
MANUFACTURER  
GUARANTEE



**Product number** 1171250544  
**EAN** 4007123684830

## TECHNICAL DATA

|                                |                                                                                     |
|--------------------------------|-------------------------------------------------------------------------------------|
| <b>Cable quality</b>           | Rubber-Neoprene                                                                     |
| <b>Luminous flux</b>           | 5800 lm                                                                             |
| <b>Power consumption</b>       | 50 W                                                                                |
| <b>Lichtausgabe</b>            | 144 lm/W                                                                            |
| <b>Energy efficiency class</b> |  |
| <b>Colour rendering index</b>  | 80-89 (class 1B)                                                                    |

|                                        |               |
|----------------------------------------|---------------|
| <b>Min.-Max. Nominal input voltage</b> | 220 V - 240 V |
| <b>Cable length</b>                    | 5 m           |
| <b>Cable designation</b>               | H07RN-F 3G1,0 |
| <b>Impact strength</b>                 | IK08          |
| <b>Protection class</b>                | I             |
| <b>Degree of protection (IP)</b>       | IP65          |
| <b>Colour</b>                          | black         |

## PACKAGING, DIMENSIONS AND WEIGHTS

|                                              |                         |
|----------------------------------------------|-------------------------|
| <b>UP</b>                                    | 1                       |
| <b>Weight of product (without packaging)</b> | 3.95 kg                 |
| <b>Dimension LxWxH (without packing)</b>     | 17 cm x 19 cm x 71.5 cm |

|                                                |                         |
|------------------------------------------------|-------------------------|
| <b>Weight of product (including packaging)</b> | 4.75 kg                 |
| <b>Dimension LxWxH (incl. packing)</b>         | 18 cm x 20 cm x 72.5 cm |