

PVC Cable	No. of Cond.	AWG	Jacket Characteristics	ID Number	Ship Wt. (lbs)	Cond. Colors	Shield	UL	CSA	Type	MSHA	Temp. (°C)
	3	20	5.1 mm OD, PVC, YE, 300 V	RF50674-30M RF50674-100M RF50674-200M	3 10 19	BN, BU, BK		•	•	AWM 2517		105° -40°
	3	20	5.1 mm OD, PVC, BK, 300 V	RF50795-30M RF50795-100M RF50795-200M	3 10 29	BN, BU, BK		•	•	AWM 2517		105° -40°
	3	20	5.1 mm OD, PVC, GY, 300 V	RF50829-30M RF50829-100M RF50829-200M	3 10 19	BN, BU, BK		•	•	PLTC AWM 2517		105° -30°
	3	20	5.7 mm OD, PVC, GY, 300 V	RF50611-30M RF50611-100M RF50611-200M	4 10 20	BU, BK, BN, Drain (22)	Foil/Drain	•	•	ITC/PLTC AWM 2517		105° -30°
	3	22	5.7 mm OD, PVC, YE, 300 V	RF50535-30M RF50535-100M RF50535-200M	4 12 23	GN, RD/BK, RD/WH	Braid	•	•	AWM 20838		105° -40°
	3	22	5.1 mm OD, PVC, YE, 300 V	RF50531-30M RF50531-100M RF50531-200M	3 9 18	GN, RD/BK, RD/WH		•	•	AWM 2517	•	105° -40°
	3	24	4.4 mm OD, PVC, BK, 300 V	RF50585-30M RF50585-100M RF50585-200M	2 7 13	BN, BU, BK		•	•	AWM 2517	•	105° -40°
	3	24	4.4 mm OD, PVC, YE, 300 V	RF50642-30M RF50642-100M RF50642-200M	2 7 13	BN, BU, BK		•	•	AWM 2517	•	105° -40°
	3	24	4.4 mm OD, PVC, GY, 300 V	RF50752-30M RF50752-100M RF50752-200M	2 7 13	BN, BU, BK		•	•	AWM 2517		105° -40°
	3	24	4.4 mm OD, PVC, YE, 300 V	RF50882-30M RF50882-100M RF50882-200M	2 7 13	BN, BU, BK		•	•	AWM 2517 CL2		105° -30°
	3	24	3.8 mm OD, PVC, YE, 300 V	RF51253-30M RF51253-100M RF51253-200M	2 6 11	BN, BK, BU		•	•	AWM 2517		105° -40°
	4	8	18.8 mm OD, PVC, YE, 600 V	RF51279-30M RF51279-100M RF51279-200M	29 96 192	RD, GN, BK, WH		•	•	AWM 2839, TC-ER		90° -40°
	4	8	20 mm OD, PVC, YE, 600 V	RF51313-30M RF51313-100M RF51313-200M	30 100 200	WH, BK, RD, GN	Braid	•	•	AWM 2839 TC-ER		90° -40°
	4	10	19.2 mm OD, PVC, BK, 600 V	RF51666-30M RF51666-100M RF51666-200M	37 123 247	BK, GN, RD, WH		•	•	STOOW, TC-ER		90° -40°
	4	12	17.7 mm OD, PVC, BK, 600 V	RF51668-30M RF51668-100M RF51668-200M	32 107 212	BK, GN, RD, WH		•	•	STOOW, TC-ER		90° -40°
	4	14	15.4 mm OD, PVC, BK, 600 V	RF51672-30M RF51672-100M RF51672-200M	26 87 173	BK, GN, RD, WH		•	•	STOOW, TC-ER		90° -40°
	4	14	10 mm OD, PVC, BK, 600 V	RF51193-30M RF51193-100M RF51193-200M	11 36 72	WH, GN, BK, RD		•	•	AWM 2839 TC-ER		90° -40°
	4	16	9.6 mm OD, PVC, YE, 600 V	RF51220-30M RF51220-100M RF51220-200M	11 36 72	RD, WH, BK, GN		•	•	AWM 2586 TC-ER		105° -40°
	4	16	11 mm OD, PVC, YE, 600 V	RF50538-30M RF50538-100M RF50538-200M	12 39 77	BK, WH, RD, GN		•	•	STOW	•	105° -40°
	4	16	11 mm OD, PVC, YE, 600 V	RF50626-30M RF50626-100M RF50626-200M	12 39 77	GN/YE, BU, BN, WH		•	•	STOW	•	105° -40°
	4	18	7.2 mm OD, PVC, YE, 300 V	RF50548-30M RF50548-100M RF50548-200M	6 18 36	BK, BU, BN, WH		•	•	AWM 2517	•	105° -40°