

296277

Ultra Hygienic Handle, Ø34 mm, 1500 mm, Lime



Thanks to a fully-moulded construction, food contact-approved materials and easy cleaning and drying, this Ultra Hygienic Handle ensures a high level of hygiene and minimises the risk of cross contamination.

Technical Data

Item Number	296277
Material	Polypropylene Glass reinforced
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	500 Pcs.
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	1520 mm
Box Width	200 mm
Box Height	80 mm
Product Diameter	34 mm
Length/Depth	1500 mm
Gross Weight	0,52 kg
Net Weight	0,48 kg
Cubik metre	0,0014 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. usage temperature (for food contact)	40 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "7", Miscellaneous Plastics	Yes
GTIN-13 Number	5705022013834
GTIN-14 Number (Box quantity)	15705028013842
Commodity Code	96039010
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.