



Product-Nr.	157210-01
EAN:	4260556627465
Model:	VARILED II Power
Order number:	157210-01
Model:	VARILED II Power
Illuminant:	LE-249p
Power consumption:	12 W
Lamp luminous flux:	1899 lm
Lamp luminous efficiency:	155 lm/W
Light distribution:	direct
Light colour:	5600K 3-step MacAdam
Number of poles:	3
Connected load:	24V DC $\pm$ 10%
Power supply:	external
Connection (connector):	M8 A-coded
Degree of protection:	IP67
Class of protection:	III
Operating temperature:	-30 °C - +60 °C (-22 °F - 140 °F)
Storage temperature:	-20 °C - +80 °C (-4 °F - 176 °F)
Colour rendering (Ra):	>85
Lamps lifetime:	> 100,000 h (L80/B10)
Housing material:	aluminium and glass
Height [B] x Width [C]:	13,7 mm x 40,2 mm (~0,54" x ~1,58")
Length [A]:	298 mm (~11,73")
Mounting:	direct
Weight (net):	300 g (~11 oz)
Gross weight:	360 g (~13 oz)
Risk group (DIN EN 62471):	free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	optional via accessories
Mounting accessories:	no
Made in:	Germany