

Kodak ESP·C110

All-in-One Printer

Print, Copy and Scan



Affordable printing now comes at an incredible price.

High-quality, low-cost ink cartridges are a Kodak standard. Now an unbelievably affordable printer is too. The KODAK ESP C110 All-in-One Printer works with the expanded line of KODAK Pigment-Based 30 Series Inks – giving you the lowest total ink replacement cost.¹ Plus, the C110 Printer delivers crisp, sharp text documents, brilliant graphics, and KODAK Lab-Quality Photos² that dry instantly and last a lifetime.³ With Kodak it's never been easier to put high-quality home printing within your means.

- Ideal for everyday printing
- Delivers crisp, sharp documents and graphics and KODAK Lab-Quality Photos² that last a lifetime³
- With KODAK All-in-One Home Center Software, you can edit with ease to reduce red eye, fix blemishes and skin tones, or even restore colour⁴
- Scan multiple pictures simultaneously – software creates separate files automatically
- Use the find photos sort features to easily find and view your memory card by month, day, or year via the printer LCD
- View and print photos without a computer using the 1.5" colour display and media card slot – supports SD, MMC, and MEMORY STICK
- Perfect Page technology – improves the quality of your scanned document even when your original is less than perfect



Memory card reader



1.5" LCD screen



Print, Copy, Scan



Automatically optimises printer settings



Lab-Quality photos² last a lifetime³

¹ As compared to leading consumer inkjet printers using manufacturers' recommended standard ink cartridges available in single-quantity pricing (i.e., no multi-packs, high capacity, combo packs, value packs or special promotions); excludes printers that use only one cartridge. Based on independent third-party price survey data obtained Q1 2011. ² Using KODAK Ultra Premium and KODAK Premium Photo Papers. ³ Under all common consumer display and storage environments. Based on testing by Wilhelm Imaging Research (WIR). ⁴ Not available on MACINTOSH OS.

Kodak ESP C110

All-in-One Printer

Print Specifications	
Print speed	- Photos: borderless KODAK Lab-Quality 10 x 15 cm (4" x 6") photos in as little as 38 seconds¹ - Documents: 20 ppm²/6 ipm³ in black/20 ppm²/4 ipm³ colour
Print resolution	9600 optimised dpi⁴ for high-resolution colour photo printing / 1200 x 1200 dpi For best monochrome text resolution (default)
Paper size	- Borderless photos from 10 x 15 cm (4" x 6") up to 210 x 297 mm (A4 Size) - Documents from 10 x 15 cm (4" x 6") up to 210 x 297 mm (A4 Size)
Paper capacity	Rear feed paper tray holds 100 sheets of document paper or 20 sheets of photo paper
Supported memory card formats	Print without a computer using memory card card formats slots – SECURE DIGITAL (SD)/ SECURE DIGITAL High Capacity (SDHC), MULTIMEDIA CARD (MMC), MEMORY STICK (MS)/MEMORY STICK PRO (PRO)

Copy Specifications	
Copy speed	5 copies per minute in black⁶/3 copies per minute in colour⁶
Copy features	- Copy up to 210 x 297 mm (A4) - Up to 99 copies at a time on a 20-100% scaling or fit-to-page range

Scan Specifications	
Resolution	1200 dpi optical scanner (CIS), 24-bit 9600 interpolated dpi
Scan features	- Scan multiple photos at once and get separate files automatically - Scan and edit documents with optical character recognition⁷

General Specifications	
Connectivity	USB 2.0 High Speed
Display	1.5" (38 mm) LCD (colour)
Power consumption	ENERGY STAR qualified
Dimensions/weight	- Printer: 419 x 173 x 312 mm (WxHxD) (16.5 x 6.8 x 12.3) - Printer weight: 11.9 lbs (5.4 kg) (includes power supply/ink/printhead) - Package: 7.75 x 18.3 x 13.77 (LxWxD) (197 x 465 x 350 mm) - Package weight: 14.55 lbs (6.6 kg)

System Requirements
WINDOWS - MICROSOFT WINDOWS 7, VISTA, or XP-Home (SP2 or above) - INTERNET EXPLORER 6 or higher - INTEL CELERON 1.2 GHz or compatible processor 512 MB memory 500 MB available hard disk space - CD-ROM drive - USB port MACINTOSH - MACINTOSH OS 10.4.8 or higher - POWERPC G4, G5, or INTEL Processor-based MAC 1.2 GHz clock speed 512 MB memory⁹ 200 MB available hard disk space - CD-ROM drive - USB port rear Note: An Intel-based MAC with 1024 Mb of RAM is recommended

Printers			
Ordering Information	Cat. No.	EAN	Pallet / Case Qty
KODAK ESP C110 All-in-One Printer	3953858	041773953858	12
Recommended Accessories			
KODAK USB 2.0 Inkjet Printer Cable A/B	845 9828	041778 45982 9	12
Ink			
KODAK Black Ink Cartridge/30B	3952330	041773952332	12
KODAK Colour Ink Cartridge/30CL	8898033	041778898031	12
KODAK Combo Ink Cartridge/30B/30CL	8039745	041778039748	10
KODAK Black XL Ink Cartridge/30BXL	3952363	041773952363	12
Papers			
Ultra Premium Photo Paper 20 Sheet 10 x 15 cm Studio Gloss	3941408	041773941404	32
Ultra Premium Photo Paper 20 Sheet 10 x 15 cm	3936754	04177393675 2	32
Ultra Premium Photo Paper 60 Sheet 10 x 15 cm	3943131	041773943132	14
Ultra Premium Photo Paper 20 Sheet 13 x 18 cm	3937950	041773937957	10
Ultra Premium Photo Paper 20 Sheet 210 x 297 mm	3936788	041773936783	10
Ultra Premium Photo Paper 50 Sheet 210 x 297 mm	3936796	041773936790	10
Premium Photo Paper 20 Sheet 10 x 15 cm	3937745	04177393774 2	32
Premium Photo Paper 60 Sheet 10 x 15 cm	3937752	041773937759	14
Premium Photo Paper 20 Sheet 210 x 297 mm	3937729	041773937728	10
Photo Paper 100 Sheet 10 x 15 cm	3937232	041773937230	14
Photo Paper 60 Sheet 10 x 15 cm	3937224	041773937223	21
Photo Paper 20 Sheet 210 x 297 mm	3937182	041773937186	10
Photo Paper 100 Sheet 210 x 297 mm	3937208	041773937209	5



For more information on the KODAK ESP C110 All-in-One Printer, visit www.kodak.com/go/aio



Memory card reader



1.5" LCD screen



Print, Copy, Scan



Automatically optimises printer settings



Lab-Quality photos² last a lifetime³

¹ Based on fastest document print mode and borderless 4 x 6 in. photos using KODAK Ultra Premium Photo Paper, Studio Gloss, and using WINDOWS OS-based PCs that meet recommended system requirements. Actual results may vary. ² Based on fastest document print mode using WINDOWS OS-based PCs that meet recommended system requirements. Actual results may vary. ³ Based on ISO/IEC 24734 testing. Actual results may vary. ⁴ Colour ink droplets to be placed with a horizontal pitch of 1/9600 inch at a minimum. Resolution may vary based on printer driver setting. ⁵ Compatible with iPhone (with OS 2.2 or later) and iPod touch (2nd generation) and iPad. ⁶ Based on ISO/IEC 24735 testing. Actual results may vary. ⁷ Not available on MACINTOSH OS. ⁸ An INTEL Processor-based MAC with 1024 MB of RAM is recommended.

© Kodak 2011. Kodak, Kodacolor, and ESP are trademarks of Eastman Kodak Company.

