



ENGLISH

Datasheet

Stock No: 821-469

RS Pro Stainless Steel Extension Spring



Product Details

Stainless Steel Extension Springs

Material to DIN 17224 No. 1 4310 or BS2056 EN58A with a right hand helix

All dimensions conform to DIN 2097 (Grade 2)

Specifications:

Material	Stainless Steel
Free Length	26.40mm
Maximum Extended Length	41.10mm
Outside Diameter	3.5mm
Wire Diameter	0.55mm
Initial Tension	13.1N
Spring Rate	0.75N/mm