

Black nitrile exam gloves for dirt-masking hand protection and superior grip

- **Masks stains:** MICROFLEX™ 93-852 exam gloves' black color disguises dirt while enhancing the visibility of light-colored objects
- **Enhanced grip:** A fully textured, non-foaming design ensures these powder- and silicone-free nitrile gloves have superior grip
- **Proven protection:** These medical exam gloves are approved for use against fentanyl and gastric acid (vomit), ensuring they are suitable for hazardous overdose situations — they also comply with EN ISO 374 Type B chemical resistance standards for chemical splash protection
- **Genuine versatility:** These gloves are suitable for various applications, used notably by auto mechanics, maintenance workers and law enforcement officers
- **Food handling compliant:** Also ideal for a wide range of food handling applications



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences

Recommended For

- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Tire rotation & changes
- Sample taking and processing
- Raw material sample collection
- Weighing and dispensing of solid and liquid raw materials
- Oil, fluids and filter change
- Maintaining lab furniture and equipment
- Inspection (picking, checking and marking)
- Inspection, selecting, checking parts
- Engine transmission and repair
- Blending, compounding solids and liquids

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
External Glove Surface	Fully Textured
Audit Standards	ISO 13485:2003
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, CE 0493, EC 2023/2006, EC 1935/2004, EN 455 1-4, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, ISO 11193, ISO 18889:2019, UKCA, EU Food Contact Approved
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	Robust
Antistatic	Yes EN1149
Silicone Free	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.65		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-2
Palm Thickness (mm/mils)	0.12/4.7		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.15 / 5.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Elongation at Break (%)	600	500	ASTM D412
Force at break (N)	7	6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93852060	93852070	93852080	93852090	93852100	93852110

Performance Standards and Regulatory Compliance

CE 0493

MD



EN ISO 374-1:2016
Type B



J K T

EN ISO 374-5



VIRUS

ISO 18889



G1

UK
CA

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region
MY: +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region
BR: +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

