


Datasheet


New5.0mm Plug Board edge

RS Stock 874-5534




Dimensions: (mm)





5.00(XX-1)+3.70



ENGLISH

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.




Specifications

- Rated Voltage: 300V 10A
- Insulation Withstands Voltage: AC 2000 V/ Min
- Contact Resistance: 20 Ω
- Insulation Resistance: 500ΩM or more at DC500V
- Temperature Range: -40°C ~ +105°C
- Torque: 0.5Nm (4.5Lb.in)
- Strip Length: 7-8mm
- Pitch: 5.0mm
- Poles: 2P-24P

Materials

- Housing: PA66 / UL94V-0
- Wire Guard: Brass / Ni Plated
- Clamp: Phosphor Bronze / Ni Plated
- Screws: M3 o , Steel Zinc Plated



P.C.B. LAYOUT

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH