

# XCKT2145N12

Limit Switch , Adjustable Lever Arm with Thermoplastic Roller (ZCY45)



List Price \$76.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

## Technical Characteristics

Actuation	CW and CCW
Actuator Action	Momentary
Actuator	Adjustable Lever Arm with Thermoplastic Roller (ZCY45)
Head Type	Rotary (ZCE01)
Operating Torque/Force	14.16 Inch-Ounces (0.10Nm)
Lever Arm Length	33 to 83.5mm
Marketing Trade Name	OsiSense
Maximum Actuation Speed	1.5 m/s
Roller Dimension	16 x 5.5mm
RoHS	Yes
Type	XCKT
Type of Duty	General Duty
Body Type	Compact Modular (ZCT21)
Shock Resistance	50G
Body Material	Plastic
Vibration Resistance	25G
Connection Type	Conduit Entrance (0.5" NPT)
Weight	0.342 lbs (0.155kg)
Contact Configuration	1 N.O./1 N.C.
Contact Operation	Snap Action
Positive Opening	Yes
Terminal Type	Screw Clamp
Ampere Rating	10A
Maximum Voltage Rating	240VAC/250VDC
NEMA Enclosure Rating	NEMA 1/2/4/6/12/13
Degree of Protection	IP66/67
Operating Temperature Range	-13 to 158°F (-25 to 70°C)
Approvals	UL Listed - CSA Certified - CE Marked
Conforming to Standards	CENELEC EN 50047

## Shipping and Ordering

Category	22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT
----------	---

Generated: 07/13/2010 16:28:31

Discount Schedule	T
GTIN	00785901269434
Package Quantity	1
Weight	0.45 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.