

WP-PA HF 34,5 BK - Protective hose



3241088

<https://www.phoenixcontact.com/in/products/3241088>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inside diameter: 29 mm, Total length: 25 m

Commercial data

Item number	3241088
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF7
Product key	AF7DSA
Catalog page	Page 585 (C-3-2019)
GTIN	4046356736527
Weight per piece (including packing)	3,260 g
Weight per piece (excluding packing)	3,000 g
Customs tariff number	39173200
Country of origin	DE

WP-PA HF 34,5 BK - Protective hose



3241088

<https://www.phoenixcontact.com/in/products/3241088>

Technical data

Product properties

Product type	Protective hose
Tensile strength GRP	100 N

Dimensions

External dimensions

Outside diameter	34.5 mm
------------------	---------

Internal dimensions

Internal diameter	29 mm
-------------------	-------

Material specifications

Material	PA 6
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

Cable/line

Bending radius, dynamic	120 mm
Bending radius, static	65 mm
Tensile strength	100 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
	IP69K
Ambient temperature (operation)	-40 °C ... 120 °C
Resistance to UV radiation	yes
Short-term temperature	150 °C

WP-PA HF 34,5 BK - Protective hose



3241088

<https://www.phoenixcontact.com/in/products/3241088>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/3241088>



UL Recognized

Approval ID: E86359



LR



VDE approval of drawings

DNV

Approval ID: TAE0000188_Rev-1

WP-PA HF 34,5 BK - Protective hose



3241088

<https://www.phoenixcontact.com/in/products/3241088>

Classifications

ECLASS

ECLASS-11.0	27430304
ECLASS-12.0	27430304
ECLASS-13.0	27430304

ETIM

ETIM 9.0	EC001177
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-PA HF 34,5 BK - Protective hose



3241088

<https://www.phoenixcontact.com/in/products/3241088>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



Accessories

WP-EC TPE HF 34,5 BK - Transition sleeve from hose to cable

3240979

<https://www.phoenixcontact.com/in/products/3240979>



Transition sleeve from hose to cable, material: TPE, color: black, flammability rating in acc. with UL 94: HB

WP-SC PA HF 34,5 BK - Cable protection end sleeve

3240986

<https://www.phoenixcontact.com/in/products/3240986>



Cable protection end sleeve, material: PA 6, color: black, flammability rating in acc. with UL 94: V2, inside diameter: 26.8 mm

WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-G HF IP66 PG29 BK - Protective hose screw connection

3240893

<https://www.phoenixcontact.com/in/products/3240893>

Cable gland, Pg thread, IP66 protection, straight



WP-G HF IP66 M32 BK - Protective hose screw connection

3240900

<https://www.phoenixcontact.com/in/products/3240900>

Cable gland, metric thread, IP66 protection, straight



WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-G HF IP69K PG29 BK - Protective hose screw connection

3240879

<https://www.phoenixcontact.com/in/products/3240879>



Cable gland, Pg thread, IP68/69k protection, straight

WP-G HF IP69K M32 BK - Protective hose screw connection

3240886

<https://www.phoenixcontact.com/in/products/3240886>



Cable gland, metric thread, IP68/69k protection, straight

WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-GA HF IP66 PG29 BK - Protective hose screw connection

3240921

<https://www.phoenixcontact.com/in/products/3240921>

Cable gland, Pg thread, IP66 protection, angled



WP-GA HF IP66 M40 BK - Protective hose screw connection

3240929

<https://www.phoenixcontact.com/in/products/3240929>

Cable gland, metric thread, IP66 protection, angled



WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-GA HF IP69K PG29 BK - Protective hose screw connection

3240907

<https://www.phoenixcontact.com/in/products/3240907>

Cable gland, Pg thread, IP68/69k protection, angled



WP-GA HF IP69K M32 BK - Protective hose screw connection

3240914

<https://www.phoenixcontact.com/in/products/3240914>

Cable gland, metric thread, IP68/69k protection, angled



WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-GR HF IP66 PG29 BK - Protective hose screw connection

3240949

<https://www.phoenixcontact.com/in/products/3240949>



Cable gland, Pg thread, IP66 protection, with strain relief

WP-GR HF IP69K PG29 BK - Protective hose screw connection

3240935

<https://www.phoenixcontact.com/in/products/3240935>



Cable gland, Pg thread, IP68/69k protection, with strain relief

WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-GR HF IP66 M40 BK - Protective hose screw connection

3240957

<https://www.phoenixcontact.com/in/products/3240957>



Cable gland, metric thread, IP66 protection, with strain relief

WP-BASE C PA HF 34,5 BK - Hose holder with cover

3240963

<https://www.phoenixcontact.com/in/products/3240963>



Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2

WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-BASE HF 37 - Hose clamp

3240972

<https://www.phoenixcontact.com/in/products/3240972>

Hose clamp, material: Steel, galvanized, color: black/silver



WP-BASE A PG29 - Protective hose fixing bracket

3241081

<https://www.phoenixcontact.com/in/products/3241081>

Fixing bracket for protective sleeves, fixed with two screws



WP-PA HF 34,5 BK - Protective hose

3241088

<https://www.phoenixcontact.com/in/products/3241088>



WP-GR HF IP69K M40 BK - Protective hose screw connection

3240943

<https://www.phoenixcontact.com/in/products/3240943>



Cable gland, metric thread, IP68/69k protection, with strain relief

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in