

Datasheet

Switchgear Cable

8114602
8114592
8114605
8114609
8114618
8114479



Image representative of range

Conductor: 196/0.40mm Plain Annealed Copper (Class 5 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

Insulation Radial Thickness: 1.20mm

Diameter Over Insulation: 11.50mm (Maximum)

Voltage Rating: 600/1000V

Conductor Resistance: 0.78 Ω /km @ 20°C (Nominal)

Cable Weight: 252.30 kg/km (Nominal)

Standard: BS 6231:2006