



Part Number : [5600230748](#)

Product Description : CTX50 Receptacle Terminal, Unsealed, Tin Plating, L-Grip, D-Wind, Left Payoff

Series Number : 560023

Status : Active

Product Category : Crimp Terminals



Documents & Resources

Drawings

[5600230748_sd.pdf](#)

[313025040-000.pdf](#)

Specifications

[AS-560023-001-001.pdf](#)

[AS-560023-001-CH-001.pdf](#)

[AS-560023-001-001.pdf](#)


[PS-560023-001-001.pdf](#)

[PS-560023-001-001.pdf](#)

[TS-560023-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	560023
Description	CTX50 Receptacle Terminal, Unsealed, Tin Plating, L-Grip, D-Wind, Left Payoff
Application	Power, Wire-to-Board
Product Name	CTX50
UPC	196823252914

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	14V DC

Physical

Durability (mating cycles max)	10
Gender	Female
Grip Code	L
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.069/g
Packaging Type	Reel

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.10-1.40mm
Wire Size (AWG)	N/A
Wire Size mm ²	0.35

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle Housings	<u>34791</u>
Mini50 Unsealed Dual Row Receptacles	<u>206523</u>
Mini50 Unsealed Receptacle Housings	<u>34959</u>

Application Tooling

Global

Description	Part Number
Extraction Tools for CTX50 Crimp Terminals	<u>638248600</u>
FA2 Mechanical Feed Crimp Applicator for CTX50 Unsealed Receptacle Terminals, 0.35mm ² and 22 AWG Wire	<u>2157861900</u>
FA2 Pneumatic Feed Crimp Applicator for CTX50 Unsealed Receptacle Terminals, 0.35mm ² and 22 AWG Wire	<u>2157861910</u>
Hand Crimp Tool for CTX50 Unsealed Receptacle Terminals	<u>638282000</u>