

FEATURES

- **Sintered Bronze Material:** Provides high durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Offers additional support and stability, reducing the risk of misalignment.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing versatility.
- **Compact Dimensions:** With an outside diameter of 14.04 mm and width of 6.09 mm, it fits into tight spaces.

RS PRO 9.02 mm Flanged Plain Bearing

RS Stock No: 528-030



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance in rotational and linear movements. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for various industrial uses.

General Specifications

Bore Size	9.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	14.04 mm
Width	6.09 mm

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

