

DATA SHEET

MMCPSL6AFS

Full shielded CAT6A tool less RJ45 plug compact size









- Depth: only 38 mm
- Class Ea performance
- Suitable for AWG22 cables





DESCRIPTION / APPLICATIONS

The MMCPSL6AFS CAT6A shielded RJ45 plug is designed for direct connection of IP equipment.

Its compact size makes it particularly suitable for CCTV applications or any other use in a restricted environment. It meets the requirements of class Ea and the latest PoE standard.

It can be connected without tools, and is wired in the same way as an RJ45 socket.

The MMCPSL6AFS is suitable for LAN and MAN applications up to 10 Gbits Ethernet (IEEE 802.3an).

PERFORMANCES —

CONNECTOR	SYSTEM
60603-7-51 Cat6A	TIA 568-C.2
FCC Part 68 subpart F	ISO 11801 Ed2.2 Class Ea - EN 50173-1
UL 18663	IEEE 802.3 af, at and bt (PoE / PoE+ / 4PPoE)





DATA SHEET

TECHNICAL PROPERTIES

Stranded AWG24 Dimensions : 38,2 x 15 x 15,3 mm (P x I x H)

Solid AWG24 to AWG22 Body: Zamac 360°

Cable diameter: 5,5 mm to 7,5 mm. Contacts: Phosphor - Bronze

Conductors diameter: 1,5 mm Color code: TIA 568A and TIA568B

ELECTRICAL PROPERTIES

Contact resistance : $\leq 100 \text{ m}\Omega$

Insulation resistance : $\geq 1000 \text{ M}\Omega \text{ to } 500 \text{ Vdc}$

Voltage rating: 125 Vac RMS

Insertion cycle: > 750
Operating voltage: < 72V Dc
Power rating: 90 W (4PPoE)

ORDERING INFORMATION

PART NUMBER	DESCRIPTION	PACKING
MMCPSL6AFS	Full shielded CAT6A tool less RJ45 plug compact size	Unit