

TRADELIFT – FATMAX

PRACTICE

Push-down lever to easily lift heavy loads by leverage, unlike a trigger-type mechanism

Lifts the lift plate up to 6 mm per stroke

PRECISE

Fine adjustment knob to lower the lift plate up to 2.5 mm

ROBUST

Closed metal case for durability and protection of the mechanism against dust and debris

STABLE

Enlarged base at the back for more stability

Screw holes to make an anchor point to fix the Tradelift

COMFORTABLE

Overmolded handle for better comfort and a better grip

SECURED

Full-release button embedded that prevents its accidental activation

CLEVER

Inclined edge that facilitates the sliding of the base under low objects



A 3rd HAND ON THE SITES

**LIFT – LIFT - LEVEL UP – SPREAD –
TIGHTEN – PULL OUT!!!**



STANLEY



max lifting
150 kg



WORKING HEIGHT
7-220 mm

FMHT83550-1
3 253 561 835 506



FMHT83552-1
3 253 561 835 520

