



Washable Cut F food liner  
for high dexterity and  
protection in food  
handling.

## ■ TEGERA® 916



[Learn more](#)

### CUT F LINER FOR FOOD CONTACT

This food-approved Cut F liner delivers excellent fingertip sensitivity, flexibility, and durable cut protection thanks to TEGERA® CRF® Technology. The glove is soft, washable at 90 °C/ 194 °F up to five times and suitable for repeated use. Ideal for food processing where a disposable glove is worn over a protective liner.

#### CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Comfortable

#### FUNCTIONS

- Approved for handling foodstuffs
- Extra long
- Soft
- Washable in 90° C



**PREVENTS RISK OF**

Cut injuries, Scratches, lacerations

**PRIMARY ENVIRONMENTS OF USE**

Cut risk environments, Dry environments

**PRIMARY AREAS OF USE**

Fishing industry work, Food handling, Hotel- and restaurant work, Kitchen work

**PRIMARY INDUSTRIES OF USE**

Food processing

**TYPE OF WORK**

Heavy weight

**SPECIFICATION**

TYPE Cut resistant gloves

CATEGORY Cat. II

KNITTING GAUGE (GG) 13

LINING MATERIAL CRF® Technology, HPPE, Polyester, Spandex,

Stainless steel fibre yarn

LENGTH 212-306 mm

DEXTERITY 5

COLOUR Blue

PAIRS PER: BUNDLE/CARTON 10/60

DISPLAY TYPE Bulk pack

CUFF STYLE Extended knitwrist cuff

CUFF MATERIAL Textile

CUT RESISTANCE (EN ISO 13997) Cut resistance level F

CUT RESISTANCE (EN ISO 13997) TDM: 35N

OUTER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Polyester, Stainless steel fibre yarn, Elastane

**COMPLIANCE**



EN ISO 21420:2020



TP TC 019:2011



Wash once before use for best fit

Maximum 5 wash cycles at 90°C

**FEATURES**



SIZE		ARTICLE NUMBER	EAN
10	XL	916-10	7333506015548
11	XXL	916-11	7333506015692
12	3XL	916-12	7333506015845
5	XXS	916-5	7333506014794
6	XS	916-6	7333506014947
7	S	916-7	7333506015098
8	M	916-8	7333506015241
9	L	916-9	7333506015395

**ejendals**

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com