

Product information

18V RECIPROCATING SAW



DJR183Z

| | |
|------------------------------|------------------------|
| Battery Type | Lithium-ion |
| Charging Time | 36 min |
| Body only machine | 1 |
| Voltage | 18 v |
| Battery Capacity | Up to 4.0Ah |
| Capacity in Wood | 50 mm |
| Capacity in Mild Steel Pipe | 50 mm |
| Strokes per Minute | 0 - 3000 spm |
| Stroke Length | 13 mm |
| Vibration K factor | 1.5 m/sec ² |
| Vibration: Cutting Wood | 7 m/sec ² |
| Vibration: Cutting Chipboard | 8 m/sec ² |
| Net weight | 1.7 kg |



- Single LED job light with pre-glow function
- Shoe Adjustment
- Tool less blade clamp for reciprocating saw blade. Simply turn to remove the blade.
- Two switch levers with variable speed control; Trigger switch on tool handle & Paddle switch on tool body to make operation easier at any grip position for versatile applications by using either trigger.
- Rubberized soft grip provides comfortable and sure grip.

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com