

Rittal – The System.

Faster – better – everywhere.

► **Ex enclosures**
Stainless steel, empty enclosure with screw fastened cover – KE 9302.000

Date : Dec 18, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Ex enclosures Stainless steel, empty enclosure with screw fastened cover – KE 9302.000

created: 18.12.2019 build on www.rittal.com/uk-en



Product description

Applications: Zone 1 and 2 or 21 and 22 to 94/9/EC
Ambient temperature range: -30 °C...+80 °C
The specified temperatures may be limited by the installed equipment
Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure

Material: Enclosure: Stainless steel 1.4301 (AISI 304)
Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal

Surface finish: Enclosure: Brushed, grain 240

**Protection category
IP to IEC 60 529:** IP 66

Certificates: IEC Ex PTB 09.0033U: yes
PTB 03 ATEX 1013U: yes

Supply includes: Enclosure
Cover

Basic material: Stainless steel

Product features

Dimensions: Width: 300 mm
Height: 150 mm
Depth: 80 mm

Packs of: 1 pc(s).

Weight/pack:	1.8 kg
EAN:	4028177138568
Customs tariff number:	94032080
ETIM 7.0:	EC002503
ETIM 6.0:	EC002503
eCl@ss 8.0/8.1:	27180502
eCl@ss 6.0/6.1:	27180502
Product description:	KEL Ex enclosure, WHD: 300x150x80 mm, Stainless steel 1.4301, without mounting plate, Empty enclosure with screw-fastened cover
Approvals	
Approvals:	ATEX IEC Ex
Certificates:	EAC Ex IEC
Declarations:	Manufacturer's declaration