

APC Smart-UPS On-Line, 1500VA, Lithium-ion, Rackmount 4U, 230V, 8x C13 IEC outlets, SmartSlot, Extended long runtime, Rail kit included

SRTI 1500RM4UXI I



#### Overview

Presentation	High density, double-conversion on-line power protection with long runtime.
Lead time	Usually in Stock

#### Main

IVIAIII	
Main Input Voltage	230 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V
Main Output Voltage	230 V
Other Output Voltage	220 V
Kw Rating	1350 W
rated power in VA	1500 VA
Input Connection Type	IEC 60320 C14
output connection type	8 IEC 60320 C13
Number of rack unit	4U
Cable length	6 ft (1.8 m)
Number of cables	1
Range of Product	Smart-UPS On-Line

#### **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Battery Type	Li-lon (Lithium Ion)
Battery Voltage	48V
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Battery life	510 year(s)
Battery Charge Power (Watts)	103 W rated

#### **General**

Number of power module filled slots

0



Number of power module free slots	0
product web sub-family	Lithium Ion
Redundant	No
Topology	Double Conversion Online

## **Physical**

<b>,</b>	
color	Black with silver front bezel
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	22.05 in (56 cm)
Net Weight	30.2 lb(US) (13.7 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal Vertical

# Input

Efficiency at full load	160275 V
Input Frequency	40 - 70 Hz auto-sensing

# Output

Bypass type	Built-in Bypass
Crest factor	3:1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	1500 VA
Max Configurable Power (Watts)	1350 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product Certifications	CE UK PSTI	
Marking	CE Mark	

## **Environmental**

Acoustic level	50 dBA
Online Thermal Dissipation	450 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	32104 °F (040 °C)
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage altitude	050000 ft (0.000000000015240.0000000000 m)

IP degree of protection	IP20
Relative Humidity	095 % non-condensing
Storage Relative Humidity	095 % non-condensing

## **Communications & Management**

Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Audible and visible alarms : prioritized by severity

## **Surge Protection and Filtering**

Surge energy rating 340 J

## Ordering and shipping details

GTIN 731304508953

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.65 in (24.5 cm)
Package 1 Width	23.62 in (60 cm)
Package 1 Length	31.89 in (81 cm)
Package 1 Weight	46.3 lb(US) (21 kg)

### **Contractual warranty**

Warranty 5 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

# Environmental Disclosure Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
<sup>⋯</sup> Energy efficiency	
Product contributes to saved and avoided emissions	Yes

#### Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No

# Product data sheet SRTL1500RM4UXLI

Image of product / Alternate images

#### **Alternative**













