

NSG „uClean“ Series
UCLEAN ARDL-1420 EHP
POWER TOOL DUST EXTRACTOR



Electric power tool vacuum cleaner with automatic pulse filter cleaning (during work breaks) for universal use in industry, in the workshop or on the construction site. Suitable for drilling, milling, grinding and sawing, concrete, plaster, stone, cement, wood, paints and varnishes with normal to low dust emission. For operation with or without filter bag. Antistatic equipped. With appliance socket for electric power tool. Large ON/OFF switch with automatic ON/OFF switch for power tools. With additional blowing function. Easy transport on the construction site due to the wobble-free accessory storage and parking position, best hose winding and connector fixing.



Order no.

020198

Additional filter	1 x FSS 1200 (foam), Art. no. 413297
Filter bag	1 x FBV 20, Art. no. 434827 (5 pcs.)

Features

Main filter	FPPR 3600 (polyester) dust retention capacity: 99,9 %, Art. no. 413464
Pulse filter cleaning	yes, during work breaks
Appliance socket	yes
Speed controller	yes, stepless
Filter control light	yes
Blowing function	yes
Carry handle with cable hook	yes
Hose fixing	yes
Hose winding and connector fixture	yes
Park position	yes
Tilting running gear	no
Gentle start	yes
After-running	yes
Water level detection	yes
Antistatic prepared	yes
Push handle	no
SmartStop	yes
Accessory storage	yes
Container material	ABS

Technical specifications

Power consumption (max.)	1400 Watt
Volume flow (max.)	69 l/s
Vacuum (max.)	259 mbar
Container volume (max.) Gross-Dust-Water	20/16/10 l
Sound pressure level Schalldruckpegel	72.0 db(A)
Dimensions L/W/H	43 x 39 x 55 cm
Weight	9.3 kg
Power cable length	8 (PVC, red) m
Reach	11,2 - 12,2 m