


Features

- FeCu-Ni "J" Type Thermocouples
- Max. operating temperature 400°C
- Protection tube Nickel Coated Brass
- Sensor type DIN/IEC-584 "J" FeCu-Ni
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 50mm
- Cable Length 2meter
- Tube Diameter 5mm

RS PRO Bayonet "J" Bore Type Thermocouples

RS Stock No: 0350433



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet "J" Type Thermocouples Temperature Sensor

Diameter(M): 5mm

Immersion Length(L): 50mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	"J" Type Thermocouples (DIN/IEC-584)
Protection tube material	Nickel coated brass

Mechanical Specifications

Diameter (M)	5mm
Immersion Length (L)	50mm
Cable Length (K)	2m

Electrical Connection



Thermoelement Connections

