

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability
- **Flanged Design:** Ensures easy installation and alignment
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads
- **ISO 9001:2008 Certified:** Ensures high quality and reliability

RS PRO 1.5 in Flanged Plain Bearing, Sintered Bronze

RS Stock No: 518-178



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent wear resistance and durability, making it ideal for use in demanding environments. The bearing's flanged design ensures easy installation and alignment, providing a stable and secure fit.

General Specifications

Bore Size	1.5 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.75 in
Width	1-7/8 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

