


554272 ADNGF-63-30-P-A Compact cylinder - Series from 03-2023



## 554272 ADNGF-63-30-P-A Compact cylinder - Series from 03-2023

Pos.	Part no.	Type	Note	Qty.	Unit
A	673626	ADN-63-P-A Set of wearing parts	Spare parts: 5, 9, 13, 14, 16	1	PC
1	774363	DIN 6912-M10X20-8.8 Socket head screw	Tightening torque 20 Nm / 14.8 lbf ft Use locking compound 8181258 CYBERBOND TI 7680	1	PC
2	207729	DIN 7984-M5X10-8.8 Socket head screw	Tightening torque 4.6 Nm / 3.4 lbf ft Use locking compound 8181258 CYBERBOND TI 7680	2	PC
3	8153515	ADNGF-63 Moment compensator		1	PC
4	8153436	ADNGF-63-X- Guide rod		2	PC
5	369543	WIFC1-16X20,5X4-TPE-U Wiper seal	Lubricate with 684474 LUB-KC1 during assembly	1	PC
6	658857	ADN-50/63 flange screw	Tightening torque 35 Nm / 25.8 lbf ft Use locking compound 8181258 CYBERBOND TI 7680	4	PC
7		ADNGF-63 Bearing cap	Not available separately, see position 11	1	PC
8		PSM-1012-15 Plain bearing	Not available separately, see position 11	2	PC
9		B-63X1,5-N-NBR75 O-ring ISO3601	Lubricate with 684474 LUB-KC1 during assembly Not available separately, see position A	2	PC
10		ADN-50/63 Bearing	Not available separately, see position 11	1	PC
11	8141773	ADNGF-63 Bearing cap module		1	PC
12	683598	ADN-63- - Piston rod	When ordering please specify the configuration (see type plate)	1	PC
13		BA-K01D-063 Piston module	Not available separately, see position A	2	PC
14		BA-K01F-063 Guiding band	Not available separately, see position A	1	PC
15	4760181	59,9X47,9X4,5BA-K01M-063 Ring magnet		1	PC
16		B-11,5X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A	1	PC
17	356376	13X20X4-1.0715 Ring		1	PC
18	203968	DIN 439-B-M12X1,25-04 Hex nut	Tightening torque 32 Nm / 23.6 lbf ft Use locking compound 8181258 CYBERBOND TI 7680	1	PC
19		ADN-63-X- Cylinder barrel	Lubricate with 684474 LUB-KC1 during assembly Not available	1	PC
20	1304909	ADN-63 End cap		1	PC