

CD-HF COVER 80 BU - Cover profile



3240615

<https://www.phoenixcontact.com/gb/products/3240615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, blue, halogen-free, width: 80 mm, length: 2000 mm

Commercial data

Item number	3240615
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE7442
Product key	BE7442
GTIN	4046356630313
Weight per piece (including packing)	456 g
Weight per piece (excluding packing)	334 g
Customs tariff number	39259020
Country of origin	DE

CD-HF COVER 80 BU - Cover profile

3240615

<https://www.phoenixcontact.com/gb/products/3240615>



Technical data

Dimensions

Width	80 mm
Height	2000 mm
Depth	11 mm
Length	2000 mm

Material specifications

Color	blue (RAL 5015)
Material	PC/ABS
Flammability rating according to UL 94	V0
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD-HF COVER 80 BU - Cover profile

3240615

<https://www.phoenixcontact.com/gb/products/3240615>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk