

CHERRY STREAM PROTECT KEYBOARD WIRELESS

The wireless STREAM keyboard – with a high-quality protective membrane



Models may vary from the image shown

Together, the CHERRY STREAM KEYBOARD WIRELESS and the CHERRY STREAM PROTECT MEMBRANE become the CHERRY STREAM PROTECT KEYBOARD WIRELESS. This means the keyboard offers the ability to be completely wiped clean or even disinfected, but remains very comfortable to type on.

CHERRY and ACTIVE KEY - two success stories combining proven quality and hygienic safety in perfect harmony.

The CHERRY brand stands for uncompromising reliability, durability and maximum comfort in daily use. Millions of CHERRY STREAM keyboards have proven their reliability, and not just in everyday office use. Hour after hour, day after day.

ACTIVE KEY has the highest level of expertise as a leading supplier of hygienic input devices. The specialist supplier in the CHERRY Group develops precise fitting and resistant silicone membranes for the highest hygiene standards in clinical applications.

With the STREAM PROTECT MEMBRANE from Active Key, millions of STREAM KEYBOARD users can add a customized hygienic key protection membrane to

their keyboard.

Keyboards can harbor dirt and germs, especially with frequent use. The CHERRY STREAM PROTECT KEYBOARD features a flat and completely enclosed key surface that can be easily wiped clean, removing dirt and microorganisms such as bacteria and viruses.

The key membrane can be taken off the keyboard for washing and changing. The STREAM PROTECT MEMBRANE thus effectively protects people, the keyboard and the environment.

The STREAM PROTECT KEYBOARD WIRELESS follows the design, elegance and sleekness of the CHERRY STREAM product line with the same slim design, high torsional rigidity and stability. Rubber pads and fold-out feet provide the usual firm footing. Sturdy scissor technology and the highly developed haptics of the key membrane ensure the legendary typing comfort of the CHERRY STREAM keyboards.

The 2.4 GHz wireless connection with up to 10 meters range is as reliable and uncomplicated as ever. The keyboard can be plug-and-play-connected to the PC via the receiver. The wireless connection has AES-128 data encryption. A low battery is indicated by the status LEDs integrated in the keys.

The STREAM PROTECT MEMBRANE provides hygienic protection for CHERRY STREAM keyboards in any setting, including public administration, educational institutions, schools and universities, and shared office environments.

FUNCTION AND PERFORMANCE

- Cleanliness & hygiene: Easy to clean.
- Productive work: Unbeatable typing feel
- Sustainability: Washable, changeable membrane
- Modern design: Slim profile
- Maximum ease of use: 3 integrated status indicators, perfect slip resistance, 10 office & multimedia buttons, up to 36 months battery life

- Highest quality: Abrasion-resistant key labeling, Cherry SX scissor mechanism, AES128 data encryption
- Certification: GS mark, 'Blue Angel' eco-label
- CHERRY STREAM PROTECT - For the best STREAM ever! For the protection of people, the keyboard and the environment.

TECHNICAL DATA

Weight main product:	1,020 g
Weight of product incl. packaging:	1,214 g
Dimensions product without packaging:	465 mm x 164 mm x 24 mm
Storage temperature:	-20 °C - 60 °C
Working temperature:	0 °C - 40 °C
Product approvals:	• CE • China RoHS • cURus • Windows Hardware Compatibility • UKCA
System Requirements-Hardware:	USB-A
Operating system:	• Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	• 2 x AA battery • Manual • Nano-USB-Receiver • Customer Information • Membrane • Keyboard
Reliability:	MTBF 90: > 10 Mio.
USB dongle:	yes
Number of batteries:	2
Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes
Battery charging socket:	no

Service life per key (in 20 mio. actuations million strokes):

Switching characteristics:	standard
Integrated metal plate:	yes
Volume [dB] of keyboard:	49 db
N-Key Rollover:	no
Anti-ghosting:	no
Key encryption:	no
Internal memory:	no
Actuating force [cN]:	65 cN
Actuating force tol.:	10 cN
Key labeling:	Silk screen printing on silicon membrane
Palm rest:	Palm rest not available
USB-Hub:	no
Illumination:	no
Adjustable feet:	integrated
Status LEDs:	in keys
Key technology:	Scissor
Application instructions:	- We recommend using nitrile gloves (instead of latex). This reduces the risk of allergies and avoids yellow discoloration of the product due to abrasion of the latex. - Cleaning agents based on mineral oil (e.g. petroleum spirits) must NOT be used for cleaning. - Greasy products such as hand creams or lipid replenishing balms reduce the service life of any silicone product. Regular cleaning will counteract this process.

Cleaning methods:

- Wiping with a soft cloth or a soft brush in combination with soap and water or a commercial dishwashing detergent.
- Removing the silicone membrane and separate cleaning with soap and water or a commercially available dishwashing detergent

Model number:	JD-85K
Protection class:	Standard
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed. Actual battery life is strongly depending on individual user behavior and hardware setup.

SKU / EAN / UPC	Protection class	Colour	Illumination	Layout
JK-8552BE-2 EAN 4025112106354 UPC	Standard	black	no	BE (Belgium)
JK-8552DE-2 EAN 4025112106316 UPC	Standard	black	no	DE (Germany)
JK-8552EU-2 EAN 4025112106309 UPC	Standard	black	no	EU (USA+ €-Symbol)
JK-8552FR-2 EAN 4025112106323 UPC	Standard	black	no	FR (France)
JK-8552GB-2 EAN 4025112106330 UPC	Standard	black	no	GB (United Kingdom)
JK-8552PN-2 EAN 4025112106347 UPC	Standard	black	no	PN (PanNordic)
JK-8552US-2 EAN 4025112106361 UPC 840183606961	Standard	black	no	US (USA)
JK-8552DE-0 EAN 4025112108662 UPC	Standard	white	no	DE (Germany)
JK-8552US-0 EAN UPC 840183607296	Standard	white	no	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.