

Datasheet

Festoon Cables



Description

This range of Briticent festoon lighting provides a very effective solution to illuminating large areas. Available with ES or BC lampholders, different lamp spacing options and in various lengths. Also available as complete kits.

Features

- Available in 50m and 100m lengths
- Lampholder spacing between 2m - 5m
- ES and BC lampholder options available
- Festoon kits supplied with 10 polycarbonate guards and GLS or CFL lamps
- Festoon guards and CFL lamps available as accessories
- 1 year guarantee

Range

Festoon - 50m, ES, 2m spacing	SEFL502ES
Festoon - 50m, BC, 2m spacing	SEFL502BC
Festoon - 100m, ES, 3m spacing	RS 670-2752
Festoon - 100m, BC, 3m spacing	SEFL13B
Festoon - 100m, ES, 5m spacing	SEFL15E
Festoon - 100m, BC, 5m spacing	SEFL15B
Festoon kit - 25m, BC, 2m spacing	SEFLKITBC
Festoon kit - 25m, ES, 2m spacing	RS 670-2743
Festoon kit - 25m, BC CFL, 2m spacing	RS 721-0888
Festoon kit - 25m, ES CFL, 2m spacing	RS 721-0881

Technical Specification

Voltage	110V ~ 50Hz
Lampholder	BC or ES
Lamp Wattage	60W max.
Cable size	2.5mm ²
IP Rating	IP44

Number of lampholders

SEFL502ES	25 at 2m intervals
SEFL502BC	25 at 2m intervals
RS 670-2752	33 at 3m intervals
SEFL13B	33 at 3m intervals
SEFL15E	20 at 5m intervals
SEFL15B	20 at 5m intervals
SEFLKITBC	10 at 2m intervals
RS 670-2743	10 at 2m intervals
RS 721-0888	10 at 2m intervals
RS 721-0881	10 at 2m intervals

Lamps and Accessories

60W 110V GLS lamp ES	GLS60E
60W 110V GLS lamp BC	GLS60B
13W 110V CFL lamp ES	CFL13ES
13W 110V CFL lamp BC	CFL13BC
Wire Festoon Guard	SEFG
Polycarbonate Guard	SEPC
Enclosed Guard	SEEG