

Batteries

Reference Germany	V13GA
Tension (V)	1.5
Electrochemical System	Alkaline-manganese
Capacity (mAh)	125
Diameter (mm)	11.6
Height (mm)	5.4
Weight (g)	1.8
Reference IEC	LR44
Reference USA	-
Varta Type Designation	V13GA

