

# Rittal – The System.

Faster – better – everywhere.

► **Network/server enclosures TS IT with vented door for room climate control, with 482.6 mm (19") mounting angles – DK 5509.110**

Date : Aug 19, 2014

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Network/server enclosures TS IT with vented door for room climate control, with 482.6 mm (19") mounting angles – DK 5509.110

created : 19.08.2014 build on [www.rittal.com/uk-en](http://www.rittal.com/uk-en)



## Product description

### Description:

- TS IT, vented front and rear door, 482.6 mm (19") mounting angles

### Material:

- Sheet steel

### Surface finish:

- Enclosure frame: Dipcoat-primed
- Interior installation: Dipcoat-primed
- Doors and roof: Dipcoat-primed, powder-coated

### Colour:

- Enclosure frame and panels: RAL 7035
- Interior installation: RAL 9005

### Supply includes:

- TS 8 enclosure frame with doors and roof plate
- 1 pc(s). Sheet steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges
- 1 pc(s). Sheet steel door at the rear, vertically divided, vented (vented surface area approx. 85% perforated), 180° hinges
- 1 pc(s). Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E
- 1 pair(s) Two 482.6 mm (19") mounting sections front and rear, variably mounted on support strips with quick-release fasteners
- 1 pc(s). Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate
- 4 pc(s). Spacers to raise the fan cover plate, for passive cooling (supplied loose)
- 1 set(s) Connection accessories for potential equalisation with earthing point (supplied loose)
- 50 pc(s). Multi-tooth screws M5, cage nuts M5, conductive (supplied loose)

### Note:

- Depending on the siting type and location, the door opening may vary for selected applications

### Packs of:

- 1 pc(s).

**EAN:**

- 4028177678125

## Product features

**Dimensions:**

- Width: 800 mm
- Height: 2000 mm
- Depth: 1000 mm

**Installation height for components:**

- 42 U

**Distance between levels as delivered:**

- 745 mm

**Load capacity:**


- 482.6 mm (19") level: 15000 N

**Weight:**


- 96 kg

## Approvals

**Approvals:**

-  [UL + C-UL \(EN\)](#)

**Certificates:**


-  [Certificates \(EN\)](#)

## Downloads

**Data sheets:**

-  [Technical details \(EN\)](#)

**Documentation:**

-  [Instructions \(FR, NL, IT, ES, DE, EN\)](#)

**CAD drawings:**

- Request

# Rittal – The System.

---

**Faster – better – everywhere.**

- Enclosures
- Power distribution
- Climate Control
- IT Infrastructure
- Software & services

Rittal Limited  
Braithwell Way · Hellaby Industrial Estate, Hellaby · Rotherham, S Yorks S66 8QY  
Phone: +44 (0) 1709 704000 · Fax: +44 (0) 1709 701217  
E-Mail: [information@rittal.co.uk](mailto:information@rittal.co.uk) · [www.rittal.co.uk](http://www.rittal.co.uk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP