

440 PRO SERIES

Designed to combine compactness with strength.

Dimensions meet the requirements of tooling standards ISO 691 / ISO 1711-1 / ASME B107.100 and aerospace standard SAE AS 954G.

Features and benefits

The 440 Pro series was designed to ensure maximum user safety. When critical tightening torques are reached, the spanner is distorted gradually so no brutal breaking likely to injure the user. Tightening torques guaranteed significantly above specifications of strength tooling and bolting standards ISO 898-1 (quality class 12.9).

5

440 Series Spanner Sets



The Open End of Sidchrome 440 Spanners feature the ANTISLIP design – a locking groove prevents slippage and knuckle injury.



Design features on the Ring End of the spanner - contact is concentrated on the flats of the fastener, not the corners. This provides greater torque and makes tightening easier.



Increased strength and more torque – the tensioning load is spread over a larger surface area.



One side of the ring is parallel to the shank - this allows you to locate on a smaller section of the fastener.

SCMT22295

14 Piece 440 Series Spanners - Metric

Barcode: 9311927222958

Metric Spanners

6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm



SCMT22296

5 Piece 440 Series Spanners - Metric

Barcode: 9311927222965

Metric Spanners

20, 21, 22, 23 & 24mm



SCMT22441

14 Piece 440 Series Spanners - Imperial

Barcode: 9311927224419

Imperial Spanners

1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8 & 15/16"



SCMT22442

5 Piece 440 Series Spanners - Imperial

Barcode: 9311927224426

Imperial Spanners

1, 1-1/16, 1-1/8, 1-3/16, 1/4"



440 Series Ring & Open End Spanners - Metric

Part No.	Barcode	Size
SCMT22306-440	9311927223061	6mm
SCMT22307-440	9311927223078	7mm
SCMT22308-440	9311927223085	8mm
SCMT22309-440	9311927223092	9mm
SCMT22310-440	9311927223108	10mm
SCMT22311-440	9311927223115	11mm
SCMT22312-440	9311927223122	12mm
SCMT22313-440	9311927223139	13mm
SCMT22314-440	9311927223146	14mm
SCMT22315-440	9311927223153	15mm
SCMT22316-440	9311927223160	16mm
SCMT22317-440	9311927223177	17mm
SCMT22318-440	9311927223184	18mm
SCMT22319-440	9311927223191	19mm
SCMT22320-440	9311927223207	20mm
SCMT22321-440	9311927223214	21mm
SCMT22322-440	9311927223221	22mm
SCMT22323-440	9311927223238	23mm
SCMT22324-440	9311927223245	24mm
SCMT22327-440	9311927223276	27mm
SCMT22330-440	9311927223306	30mm
SCMT22332-440	9311927223320	32mm



440 Series Ring & Open End Spanners - AF

Part No.	Barcode	Size
SCMT22510-440	9311927225102	1/4"
SCMT22511-440	9311927225119	9/32"
SCMT22512-440	9311927225126	5/16"
SCMT22513-440	9311927225133	11/32"
SCMT22514-440	9311927225140	3/8"
SCMT22515-440	9311927225157	7/16"
SCMT22516-440	9311927225164	1/2"
SCMT22517-440	9311927225171	9/16"
SCMT22518-440	9311927225188	5/8"
SCMT22519-440	9311927225195	11/16"
SCMT22520-440	9311927225201	3/4"
SCMT22521-440	9311927225218	13/16"
SCMT22522-440	9311927225225	7/8"
SCMT22523-440	9311927225232	15/16"
SCMT22524-440	9311927225249	1"
SCMT22525-440	9311927225256	1-1/16"
SCMT22526-440	9311927225263	1-1/8"
SCMT22527-440	9311927225270	1-3/16"
SCMT22528-440	9311927225287	1-1/4"

