







## 9007CA11 LIMIT SWITCH LEVER ARM 2IN C



Download your 9007CA11 datasheet



## C

Wain		- Hic
Range of product	9007	
Series name	Heavy duty	
Product or component type	Limit switch lever	
Device short name	9007C	
Associated head	9007A 9007B 9007C 9007N 9007T10 9007T5	
Associated complete product	9007AW 9007C	
Movement of operating head	Rotary	
Type of operator	Cast zinc spring return roller lever length: 2 in - offset:	
Type of roller	1 steel outside roller diameter: 0.75 in - width: 0.25 in	
Type of approach	Lateral approach	
Positive opening	Without	
Complementary ————		⊟ Hio
Switch actuation	By 30° cam	
Product weight	0.1 lb(US)	
Environment —		⊟ Hic
Ambient air temperature for operation	-20185 °F	
Ambient air temperature for storage	-20185 °F	
Environmental characteristic	Standard environment	

## Offer Sustainability

Hide

Sustainable offer status Green Premium product

RoHS (date code: YYWW) Compliant - since 1150 - Schneider Electric declaration of

conformity

Reference not containing SVHC above the threshold **REACh** 

**Product environmental** 

profile

Available download Product environmental

Product end of life instructions

Need no specific recycling operations





Period 18 months