

Features

- UL94V-2 flame-rated, UL-approved Nylon 66
- Low smoke and halogen-free
- Maximum operating temperature up to 85°C

RS PRO Extra Strong Cable Ties

RS Stock No.: 0656052



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A high-performance, super-strength nylon cable tie designed for secure and reliable bundling. Made from UL-approved Nylon 66 with a UL94V-2 flame rating, it offers excellent durability and resistance to wear, ensuring firm cable management. Low smoke and halogen-free, it is ideal for industrial, commercial, and domestic applications, withstanding temperatures up to 85°C

General Specifications

| | |
|-------------------------------|---|
| Series | Extra Strong Cable Ties |
| Type | Non-Releaseable |
| Colour | Natural |
| Material | Nylon 66 |
| Finish | N/A |
| Application | Bundling wire together / Tightening labels to poles |
| Resistant To | N/A |
| UV Resistant | Yes |
| Minimum Operating Temperature | N/A |
| Maximum Operating Temperature | 85°C |
| Fire Behaviour | Self-Extinguishing |
| Quantity | 100 |

Mechanical Specifications

| | |
|---------------------|-------|
| Length | 280mm |
| Width | 4.8mm |
| Tensile Strength | 334N |
| Maximum Bundle Dia. | 70mm |

Approvals

| | |
|---------------|---------|
| Standards Met | UL RoHS |
|---------------|---------|

