












RS Pro 22mm IP67 Circular Connectors

No. of Contacts: 3 + PE

<p>External-threaded Panel-Mount</p> <p style="text-align: center;">Stock No: 210-7303</p> 	Can mate with	<p style="text-align: center;">Internal-threaded Standard Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7317</td> <td style="text-align: left;">6.5mm</td> </tr> <tr> <td style="text-align: right;">210-7318</td> <td style="text-align: left;">8.5mm</td> </tr> <tr> <td style="text-align: right;">210-7319</td> <td style="text-align: left;">10.5mm</td> </tr> </table>	Stock No:	Cable dia.	210-7317	6.5mm	210-7318	8.5mm	210-7319	10.5mm	For in-line connection can mate with	<p style="text-align: center;">External-threaded Standard Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7296</td> <td style="text-align: left;">6.5mm</td> </tr> <tr> <td style="text-align: right;">210-7297</td> <td style="text-align: left;">8.5mm</td> </tr> <tr> <td style="text-align: right;">210-7298</td> <td style="text-align: left;">10.5mm</td> </tr> </table>	Stock No:	Cable dia.	210-7296	6.5mm	210-7297	8.5mm	210-7298	10.5mm	Can mate with	<p style="text-align: center;">Internal-threaded Panel-Mount</p> <p style="text-align: center;">Stock No: 210-7316</p> 
Stock No:	Cable dia.																					
210-7317	6.5mm																					
210-7318	8.5mm																					
210-7319	10.5mm																					
Stock No:	Cable dia.																					
210-7296	6.5mm																					
210-7297	8.5mm																					
210-7298	10.5mm																					
		<p style="text-align: center;">Internal-threaded Short Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7312</td> <td style="text-align: left;">4.5-7 mm</td> </tr> <tr> <td style="text-align: right;">210-7313</td> <td style="text-align: left;">7-12 mm</td> </tr> </table>	Stock No:	Cable dia.	210-7312	4.5-7 mm	210-7313	7-12 mm		<p style="text-align: center;">External-threaded Short Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7299</td> <td style="text-align: left;">4.5-7 mm</td> </tr> <tr> <td style="text-align: right;">210-7300</td> <td style="text-align: left;">7-12 mm</td> </tr> </table>	Stock No:	Cable dia.	210-7299	4.5-7 mm	210-7300	7-12 mm						
Stock No:	Cable dia.																					
210-7312	4.5-7 mm																					
210-7313	7-12 mm																					
Stock No:	Cable dia.																					
210-7299	4.5-7 mm																					
210-7300	7-12 mm																					
		<p style="text-align: center;">Internal-threaded 90° Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7314</td> <td style="text-align: left;">4.5-7 mm</td> </tr> <tr> <td style="text-align: right;">210-7315</td> <td style="text-align: left;">7-12 mm</td> </tr> </table>	Stock No:	Cable dia.	210-7314	4.5-7 mm	210-7315	7-12 mm		<p style="text-align: center;">External-threaded 90° Cable-Mount</p>  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: right;">Stock No:</td> <td style="text-align: left;">Cable dia.</td> </tr> <tr> <td style="text-align: right;">210-7301</td> <td style="text-align: left;">4.5-7 mm</td> </tr> <tr> <td style="text-align: right;">210-7302</td> <td style="text-align: left;">7-12 mm</td> </tr> </table>	Stock No:	Cable dia.	210-7301	4.5-7 mm	210-7302	7-12 mm						
Stock No:	Cable dia.																					
210-7314	4.5-7 mm																					
210-7315	7-12 mm																					
Stock No:	Cable dia.																					
210-7301	4.5-7 mm																					
210-7302	7-12 mm																					
<p>Use Sealing Cap No: 210-7924</p> 		<p>Use Sealing Cap No: 210-7925</p> 		<p>Use Sealing Cap No: 210-7924</p> 		<p>Use Sealing Cap No: 210-7925</p> 