


plastic pipe

PQ-PA-28X2,5X3000

Part number: 194594

FESTO

For compressed air, vacuum or liquids. Supplied in lengths of 3 m.



Data sheet

Feature	Value
Outside diameter	28 mm
Inside diameter	23 mm
Temperature dependent operating pressure	-0.95 ... 10 bar
Medium temperature	-25 ... 75 °C
Ambient temperature	-25 ... 75 °C
Product weight according to length	0.204 kg/m
Colour	Black
Material tubing	PA