


## EVC141

ADOGF030MSS0002H03

Connection technology



### Product characteristics

Socket

For sensors with

M8 connector

Free from silicone

Free from halogen

gold-plated contacts

### Electrical data

Electrical design		AC/DC
Operating voltage	[V]	50 AC / 60 DC
Current rating	[A]	3
Protection class		III

### Environment

Ambient temperature	[°C]	-25...90, cULus: max. 80 °C
Ambient temperature (moving)	[°C]	-25...90, cULus: max. 80 °C
Protection		IP 65 / IP 67 / IP 68 / IP 69K

### Mechanical data

Design		straight
Material body		housing: TPU (urethane) orange; sealing: Viton
Material nut		brass; nickel-plated
Tightening torque for knurled nut [Nm]		0.3...0.5
Drag chain suitability		<p>Bending radius for flexible applications:</p> <p>min. 10 x cable diameter max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s<sup>2</sup></p> <p>Travel speed:</p> <p>Bending cycles:</p> <p>Torsional strain:</p> <p>&gt; 5 million ± 180 °/m</p>
Weight	[kg]	0.05

### Electrical connection

Connection		PUR cable / 2 m; 3 x 0.25 mm <sup>2</sup> (32 x Ø 0.1 mm); Ø 3.7 mm; halogen-free
Sheath color		black

### Wiring





## EVC141

ADOGF030MSS0002H03

Connection technology

### Core colors

BK black  
BN brown  
BU blue



### Remarks

Pack quantity [piece] 1

ifm efector, inc. 782 Springdale Drive, Exton, PA 19341 — We reserve the right to make technical alterations without prior notice. — US — EVC141 — 30.06.2010