

ECOFLOW

RIVER 3 Plus

ID: Silver & Grey

UPS: <10 ms

Battery Pack Water Resistance Level: IP54

Volume: <30 dB in 0.5 m (1.6 ft)

Warranty: 5 Years



General

Capacity

286Wh

Dimensions

234 x 232 x 146 mm

RIVER 3 Plus Extra Battery EB300

Dimensions

286Wh capacity
234 x 224 x 110 mm

RIVER 3 Plus Extra Battery EB600

Dimensions

572Wh capacity
234 x 224 x 158 mm

Net Weight

3.5 kg

App

Supported

RIVER 3 Plus Extra Battery EB300

Expandable capacity to 572Wh

RIVER 3 Plus Extra Battery EB600

Expandable capacity to 858Wh

Output

Total Output Ports

7

Max Device(s) Power Supported by X-Boost

1200W

Car Power x 1

12.6V, 10A, 128W Max

AC x 3

3 x 600W (Surge 1200W)

USB-A x 2

2 x 12W Max

USB-C x 1

1 x 100W Max

Input

AC Charging

360W (60 Min)

Generator Charging

360W (60 Min)

Solar Charging

11~55V, 13A Max
220W Max (1.5 Hr)

Car Charging

220W (3.3 Hr)

Battery

Chemistry

LFP

Cycle Life

3000 Cycles to 80% Capacity