








MOUNTING PLATE SIZE



SHOWN WITH  
END CAP



SHOWN WITH  
STRAIN RELIEF



- REQUIRES CONTACT  
RETENTION WEDGE AW4P
- GASKET
- 2X Ø4.0, 16.4 DP FROM MATING SURFACE  
RECOMMENDED ATTACHMENT OPTIONS:  
1. HEX WASHER HEAD SHEETMETAL SCREW,  
#10, 1/2" LONG, HEX SIZE 5/16".  
2. SELF THREAD SCREW FOR PLASTIC SUCH AS ST 4.8

NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:  
HOUSING: THERMOPLASTIC; COLOR: BLACK  
END CAP: THERMOPLASTIC; COLOR: BLACK  
STRAIN RELIEF CAP: THERMOPLASTIC; COLOR: BLACK  
SEALS: SILICONE RUBBER; COLOR: RED
- MODIFICATIONS: FLANGE, GASKET, END CAP (OPT), STRAIN  
RELIEF CAP (OPT), REDUCED DIAMETER SEAL (OPT).
- SPECIFICATIONS:  
3.1 CURRENT RATING: 13 AMPS  
3.2 OPERATING TEMPERATURE: -55°C TO +125°C  
3.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2  
MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.  
3.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.  
3.5 MOISTURE RESISTANCE: IP67 ( MATED CONDITION )  
3.6 MATING CYCLE DURABILITY: 100 CYCLES  
3.7 RoHS COMPLIANT
- MATING PART: AT06-4S\* PLUG  
(\* = MODIFICATIONS )
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND REAR SEAL WIRE RANGE:

REDUCED DIAMETER SEAL:

| CONTACT<br>SIZE | MIN. INSUL<br>O.D.   | MAX. INSUL<br>O.D.   | TYPICAL<br>WIRE RANGE |
|-----------------|----------------------|----------------------|-----------------------|
| 16              | 1.35 mm<br>(.053 in) | 3.05 mm<br>(.120 in) | 14 - 20 AWG           |

STANDARD SEAL:

| CONTACT<br>SIZE | MIN. INSUL<br>O.D.   | MAX. INSUL<br>O.D.   | TYPICAL<br>WIRE RANGE |
|-----------------|----------------------|----------------------|-----------------------|
| 16              | 2.24 mm<br>(.088 in) | 3.68 mm<br>(.145 in) | 14 - 20 AWG           |

| REVISIONS |     |                          |         |     |      |
|-----------|-----|--------------------------|---------|-----|------|
| REV       | ECO | DESCRIPTION              | DATE    | BY  | APPR |
| A1        | -   | RELEASED CHARTED DRAWING | 23MAR18 | JAH | -    |

| MODIFICATIONS |              |         |               |
|---------------|--------------|---------|---------------|
| PART NUMBER   | SEAL         | END CAP | STRAIN RELIEF |
| AT04-4P-PM11  | STANDARD     | NO      | NO            |
| AT04-4P-PM12  | REDUCED DIA. | NO      | NO            |
| AT04-4P-PM13  | STANDARD     | YES     | NO            |
| AT04-4P-PM14  | REDUCED DIA. | YES     | NO            |
| AT04-4P-PM15  | STANDARD     | NO      | YES           |
| AT04-4P-PM16  | REDUCED DIA. | NO      | YES           |

|                                                                                                                                                                                    |  |                                                                                                                                                                                                                                                                                                                                                         |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| AT04-4P-PM1X                                                                                                                                                                       |  |                                                                                                                                                                                                                                                                                                                                                         |  |
| PART NUMBER                                                                                                                                                                        |  | DESCRIPTION                                                                                                                                                                                                                                                                                                                                             |  |
| QUANTITY                                                                                                                                                                           |  | ITEM                                                                                                                                                                                                                                                                                                                                                    |  |
| UNLESS OTHERWISE SPECIFIED:<br>1) All dimensions are in metric (mm).<br>2) Tolerances are as follows:<br>1 PL DEC ±0.30<br>2 PL DEC ±0.15<br>3 PL DEC ±0.08<br>3) Note reference = |  | SIGNATURES<br>DRAWN: J. HEAD<br>CHECKED:<br>ENGINEER:<br>APPROVAL:<br>CUSTOMER:<br>THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS. |  |
| MATERIAL SPECIFICATIONS:                                                                                                                                                           |  | DATE<br>23MAR18                                                                                                                                                                                                                                                                                                                                         |  |
| PROCESS SPECIFICATIONS:                                                                                                                                                            |  | Amphenol<br>Sine Systems - www.amphenol-sine.com<br>44724 Morley Drive<br>Clinton Township, MI 48036                                                                                                                                                                                                                                                    |  |
| NEXT ASSY:                                                                                                                                                                         |  | RECEPTACLE, 4 PIN, AT SERIES, W/FLANGE, GASKET                                                                                                                                                                                                                                                                                                          |  |
| SIZE<br>B C-                                                                                                                                                                       |  | DWG NO:<br>AT04-4P-PM1X                                                                                                                                                                                                                                                                                                                                 |  |
| SCALE<br>NONE                                                                                                                                                                      |  | REVISION<br>A1                                                                                                                                                                                                                                                                                                                                          |  |
| SHEET 1 OF 1                                                                                                                                                                       |  |                                                                                                                                                                                                                                                                                                                                                         |  |

# A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

| Machined Contacts, Sockets & Pins |                                        |      |       |          |
|-----------------------------------|----------------------------------------|------|-------|----------|
| Part Number                       | Description                            | Size | AWG   | Type     |
| AT60-215-1631                     | Male Contact - Pin, Gold-plated        | 16   | 14    | Machined |
| AT62-209-1631                     | Female Contact - Socket, Gold-plated   | 16   | 14    | Machined |
| AT60-215-16141                    | Male Contact - Pin, Nickel-plated      | 16   | 14    | Machined |
| AT62-209-16141                    | Female Contact - Socket, Nickel-plated | 16   | 14    | Machined |
| AT60-202-1631                     | Male Contact - Pin, Gold-plated        | 16   | 16-20 | Machined |
| AT62-201-1631                     | Female Contact - Socket, Gold-plated   | 16   | 16-20 | Machined |
| AT60-202-16141                    | Male Contact - Pin, Nickel-plated      | 16   | 16-20 | Machined |
| AT62-201-16141                    | Female Contact - Socket, Nickel-plated | 16   | 16-20 | Machined |
| AT60-202-1631-22                  | Male Contact - Pin, Gold-plated        | 16   | 22-24 | Machined |
| AT62-201-1631-22                  | Female Contact - Socket, Gold-plated   | 16   | 22-24 | Machined |
| AT60-202-16141-22                 | Male Contact - Pin, Nickel-plated      | 16   | 22-24 | Machined |
| AT62-201-16141-22                 | Female Contact - Socket, Nickel-plated | 16   | 22-24 | Machined |

| Tooling - Machined Contacts |                                                               |
|-----------------------------|---------------------------------------------------------------|
| Part Number                 | Description                                                   |
| AUTK-16                     | Hand Crimp Tool, Size 16                                      |
| AUTK-100                    | Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20 |
| CA-5D12                     | Universal Hand Crimp Tool, Size 12/16/20                      |
| CA-5E12                     | Pneumatic Crimp Tool, Size 12/16/20                           |

| Contact Removal Tools (For both Machined or Stamped & Formed Contacts) |                                        |
|------------------------------------------------------------------------|----------------------------------------|
| Part Number                                                            | Description                            |
| ATRT-100                                                               | Contact and Wedgelock Extraction Tool  |
| AT11-310-1605                                                          | Contact Removal Tool, Plastic, Size 16 |

| Sealing Plugs (For both Machined or Stamped & Formed Contacts) |                                                 |
|----------------------------------------------------------------|-------------------------------------------------|
| Part Number                                                    | Description                                     |
| A114017                                                        | Sealing Plug, Size 16, White                    |
| A114017-SR                                                     | Sealing Plug, Size 16, SR01 Series, Black       |
| AT13-217-1605                                                  | Locking Sealing Plug, Size 16, Grey             |
| AT13-217-1605-SR                                               | Locking Sealing Plug, Size 16, SR01 Series, Red |

| Stamped & Formed Contacts, Sockets & Pins |                                        |      |       |                  |
|-------------------------------------------|----------------------------------------|------|-------|------------------|
| Part Number                               | Description                            | Size | AWG   | Type             |
| AT60-14-0122                              | Male Contact - Pin, Nickel-plated      | 16   | 14-18 | Stamped & Formed |
| AT62-14-0122                              | Female Contact - Socket, Nickel-plated | 16   | 14-18 | Stamped & Formed |
| AT60-14-0144                              | Male Contact - Pin, Gold-plated        | 16   | 14-18 | Stamped & Formed |
| AT62-14-0144                              | Female Contact - Socket, Gold-plated   | 16   | 14-18 | Stamped & Formed |
| AT60-16-0122                              | Male Contact - Pin, Nickel-plated      | 16   | 16-18 | Stamped & Formed |
| AT62-16-0122                              | Female Contact - Socket, Nickel-plated | 16   | 16-18 | Stamped & Formed |
| AT60-16-0144                              | Male Contact - Pin, Gold-plated        | 16   | 16-18 | Stamped & Formed |
| AT62-16-0144                              | Female Contact - Socket, Gold-plated   | 16   | 16-18 | Stamped & Formed |
| AT60-16-0622                              | Male Contact - Pin, Nickel-plated      | 16   | 16-20 | Stamped & Formed |
| AT62-16-0622                              | Female Contact - Socket, Nickel-plated | 16   | 16-20 | Stamped & Formed |
| AT60-16-0644                              | Male Contact - Pin, Gold-plated        | 16   | 16-20 | Stamped & Formed |
| AT62-16-0644                              | Female Contact - Socket, Gold-plated   | 16   | 16-20 | Stamped & Formed |
| AT60-16-0677                              | Male Contact - Pin, Tin-plated         | 16   | 16-20 | Stamped & Formed |
| AT62-16-0677                              | Female Contact - Socket, Tin-plated    | 16   | 16-20 | Stamped & Formed |
| AT60-16-0822                              | Male Contact - Pin, Nickel-plated      | 16   | 20-22 | Stamped & Formed |
| AT62-16-0822                              | Female Contact - Socket, Nickel-plated | 16   | 20-22 | Stamped & Formed |
| AT60-16-0844                              | Male Contact - Pin, Gold-plated        | 16   | 20-22 | Stamped & Formed |
| AT62-16-0844                              | Female Contact - Socket, Gold-plated   | 16   | 20-22 | Stamped & Formed |

| Tooling - Stamped & Formed Contacts |                                     |
|-------------------------------------|-------------------------------------|
| MF3-3950                            | Crimp Die - Size 16, 18-20AWG       |
| MF3-3953                            | Crimp Die - Size 16, 16-18AWG       |
| MF3-3975                            | Crimp Die - Size 16, 14-16AWG       |
| MF3-3990                            | Crimp Die - Size 16, 20-22AWG       |
| ATT-16-00                           | Hand Crimp Tool - Size 16, 14-16AWG |
| ATT-16-01                           | Hand Crimp Tool - Size 16, 18-20AWG |
| ATT-1612-03                         | Hand Crimp Tool - Size 16, 20-22AWG |