

8.4" Open Frame

Part No	:	HE084AOT4
Item Description	:	8.4" monitor / 4 wire resistive touch

Advantage and Application	Item	Description
<ul style="list-style-type: none"> ■ long term availability of adopted TFT LCD panels (stability of supply for min. 3 years) ■ Analog RGB / DVI supportable ■ 4 wire resistive touch adopted ■ RS232 communication (option) ■ Fine finishing metal chassis (brilliant design & complete set level OSD button) ■ Application <ul style="list-style-type: none"> - Kiosks - ATMs - Casino & Amusement games - Lottery and Ticket sales - Self-Services - Industrial process control 	Frame / bezel Color	EGL in black
	Display Type	Size: 8.4" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
	Active area	170.4 (H) x 127.8 (V)
	Optimal (native) resolution	800 x 600
	Support color	16.2 M colors
	Brightness (without touch)	450 cd/m2
	Viewing Angles	80 / 80 / 80 / 60
	Input video supportable	Analog RGB, DVI, Audio (option, 2W x 2W)
	Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
	Mounting Holes	VESA standard mounting 75 x 75 mm
	Applicable Graphic Mode	VESA standard timing control
	Weight & Volume	Unit Weight : 1,400 g, Carton Packing : pcs Carton weight : Kg

