



Main

Range	Mureva
Range of product	Mureva lights
Product name	Floodlight
Product or component type	Lamp
Device application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

Complementary

Type of installation	Outdoor
Total system power	20 W
Light source	LED
[Ue] rated operational voltage	230 V AC
Power factor	0.9
Colour rendering index	R _a =80
Luminous flux	2000 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Colour	Black
Provided equipment	Sensor
Beam angle	110 °
Shape	Rectangular
Height	163.4 mm
Width	181.4 mm
Depth	26.0 mm
Net weight	570 g

Environment

Environmental characteristic	Weatherproof
IP degree of protection	IP44
IK degree of protection	IK04
Ambient air temperature for operation	-30...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	630 g
Package 1 Height	19.2 cm
Package 1 width	19.2 cm
Package 1 Length	19.2 cm
Unit Type of Package 2	S04
Number of Units in Package 2	10

Package 2 Weight	7.003 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Weight	68.024 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins